


1. MATERIALS AND FINISHES:  
TNC STR BHD JACK FRONT MOUNT IP 67 - BRASS, ELECTROLESS NICKEL PLATING



CABLE - 1.13 MM CABLE

2. ELECTRICAL:  
A. IMPEDANCE: 50 OHM

3. PACKAGING:  
A. QUANTITY: SINGLE PACK  
B. MARKING: BAG TO BE MARKED  
"AMPHENOL RF, 95-850-281-XXX AND DATE CODE"



### RECOMMENDED MOUNTING HOLE DIMENSIONS



LENGTH TABLE	
PART NUMBER (IMPERIAL)	LENGTH AND TOLERANCE 'L' IN MM (INCHES)
95-850-281-050	50.00 ± 3.81 [1.969 ± 0.150]
95-850-281-100	100.00 ± 3.81 [3.937 ± 0.150]
95-850-281-150	150.00 ± 3.81 [5.906 ± 0.150]
95-850-281-200	200.00 ± 5.08 [7.874 ± 0.200]
95-850-281-250	250.00 ± 5.08 [9.843 ± 0.200]
95-850-281-300	300.00 ± 5.08 [11.811 ± 0.200]

<input checked="" type="checkbox"/> FREQUENCY: DC - 6 GHz	<input checked="" type="checkbox"/> CONTINUITY
<input type="checkbox"/> VSWR: ____ MAX.	<input checked="" type="checkbox"/> HI-POT: 200 VRMS
<input type="checkbox"/> INS. LOSS: ____ dB MAX.	<input type="checkbox"/> OTHER:

NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE METRIC (INCHES) AND TOLERANCES ARE:

<0.5mm = ±0.05mm	[<0.020 = ±0.002]
>0.5 - 6mm = ±0.1mm	[>0.020 - 0.236 = ±0.004]
>6.00 - 30mm = ±0.2mm	[>0.236 - 1.181 = ±0.008]
>30.00 - 120mm = ±0.3mm	[>1.181 - 4.725 = ±0.012]

MATERIAL
----------

SEE NOTES

ENGR.1  
CLEMENT

---

ENGR.2

DATE	07-JUL-21
------	-----------

TITLE
-------

TNC STR BHD JACK FRONT MOUNT  
IP 67 TO AMC4 RA PLUG  
USING 1.13 MM CABLE  
VARIOUS LENGTH

SHEET NO. 2 OF 2


SCALE: 4.5:1.0

# Amphenol RF

SIZE  B	DRAWING NO.	95-850-281-XXX
	ITEM NO.	95-850-281-XXX
	PART NO.	95-850-281-XXX

A

THIRD ANGLE PROJ.



REFERENCE
95-850-264-XXX

EAR#	10783
------	-------

ANGLES =  $\pm 1^\circ$

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[095-850-281-150](#) [095-850-281-200](#) [095-850-281-250](#) [095-850-281-100](#) [095-850-281-300](#) [095-850-281-050](#)