

CONNECTOR BODY: PHOSPHOR BRONZE, AU 0.05 um MIN. PLATED OVER NI 1.0 um MIN.
CONNECTOR CENTER CONTACT: PHOSPHOR BRONZE , AU 0.1 um MIN. PLATED OVER NI 1.0 um MIN.
CONNECTOR INSULATOR: PBT, UL94V-0, BLACK
CABLE JACKET: FEP
CABLE DIELECTRIC: FEP
CABLE CENTER CONDUCTOR: COPPER WIRE STRANDED, SILVER PLATED
CABLE OUTER CONDUCTOR: COPPER WIRE BRAID, TIN PLATING

Technical drawing of a cross-section of a component. The drawing shows a symmetrical profile with a central rectangular opening. The top edge is flat, and the bottom edge features a series of horizontal lines, possibly indicating a layered or reinforced structure. A dimension line at the top indicates a width of 3 ± 0.2 . The drawing is centered on a vertical axis, indicated by a dashed line.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1°					MATERIAL	DRAWN	DATE	TITLE AMC PLUG TO AMC PLUG JUMPER ASSEMBLY ON 1.13MM CABLE		Amphenol RF www.amphenolrf.com	
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.						JEKY	29-Jan-19				
						ENGINEER	DATE				
						FIGO	29-Jan-19				
						APPROVED	DATE	SCALE: 3.0:1.0	SHEET 2 OF 2		
REF:					FIGO	14-Feb-19					
CONFIGURATION LEVEL: In Work					CAD FILE	DWG SIZE		REV			
FINISH						B		H			
DRAWING NO. A-1PAX113-XXXXZ											
ITEM NO. A-1PAX113-XXXXZ											
PART NO. A-1PAX113-XXXXZ											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[A-1PA-113-050B2](#) [A-1PA-113-077B2](#) [A-1PA-113-330B2](#) [A-1PA-113-137B2](#) [A-1PA-113-064B2](#) [A-1PA-113-305B2](#)
[A-1PA-113-390B2](#) [A-1PA-113-095B2](#) [A-1PA-113-410B2](#) [A-1PA-113-370B2](#) [A-1PA-113-205B2](#) [A-1PA-113-048B2](#) [A-](#)
[1PA-113-999B2](#) [A-1PA-113-400B2](#) [A-1PA-113-153B2](#) [A-1PA-113-204B2](#) [A-1PA-113-085B2](#) [A-1PA-113-279B2](#) [A-](#)
[1PA-113-150G2](#) [A-1PA-113-084B2](#) [A-1PA-113-01KB2](#) [A-1PA-113-089B2](#) [A-1PA-113-356B2](#)