

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 42977	04/19	GPF

MATERIAL:

CONNECTORS:

CABLE:

SHRINK TUBING:

2.4MM PLUG (SF1611-60001)

SMPS JACK (3821-40001)

FLEXIBLE Ø.047 CABLE

M23053/5

SV P/N	OAL
7016-0074	6.000
7016-0075	12.000

PERFORMANCE:

IMPEDANCE:

FREQ. RANGE:

50 OHMS

DC TO 50.0 GHz

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63. MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	Amphenol SV MICROWAVE 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409	
FINISH:	SEE NOTES	FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15'			
SURFACE AREA:	N/A	DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005			
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994		TITLE: 2.4mm PLUG TO SMPS JACK FOR FLEXIBLE Ø.047 CABLE ASSEMBLY	
		THIRD ANGLE PROJECTION	DRAWN: SJ 04/01/19	SIZE B	CAGE CODE 95077
			CHECKED: GPF 04/01/19	DWG. NO. 7016-0074-0075	
			APPROVED: GPF 04/01/19	SCALE: 2:1	
				SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7016-0074](#)