

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 42984	04/19	GPF

MATERIAL:

CONNECTORS:

CABLE:

SHRINK TUBING:

SMMP JACK (3221-40006)

SMA PLUG (SF2906-6002)

T-FLEX 405

M23053/5

SV P/N	OAL
7032-7526	6.000
7032-7527	12.000


PERFORMANCE:

IMPEDANCE:

FREQ. RANGE:

50 OHMS

DC TO 18.0 GHz

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63. MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	<div> 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409</div> <div>TITLE: SMMP JACK TO SMA PLUG FOR Ø.085 T-FLEX 405 CABLE ASSEMBLY</div>	
FINISH:	SEE NOTES	FRACTIONAL: ±1/64    ANGULAR: X° ±1°0'    X°X' ±15'			
SURFACE AREA:	N/A	DECIMAL: .X    ±.030 .XX    ±.010 .XXX    ±.005			
PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994			
THIRD ANGLE PROJECTION		DRAWN: SJ 04/24/19	SIZE B	CAGE CODE 95077	DWG. NO. 7032-7526-7527
		CHECKED: GPF 04/24/19	SCALE: 2:1		SHEET 1 OF 1
		APPROVED: GPF 04/24/19			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7032-7527](#)