

# Amphenol®



## Amphenol® NEPTUNE® Rugged Environment Connector featuring RADSOK® Contacts.

Amphenol Industrial Operations introduces a new power connector family featuring Amphenol's exclusive RADSOK® contact system. The new NEPTUNE® connector series is designed to perform in the most demanding environments.


NEPTUNE® incorporates our RADSOK® contact technology. The RADSOK® system is a patented electrical terminal based on a hyperbolic grid configuration. As a male pin is inserted, the grid deflects, imparting high normal forces. The hyperbolic configuration ensures a large coaxial, face-to-face engagement area for a low milli-volt drop connection with low insertion force. The stamped grid and cylinder are very rugged, allowing for a high quantity of insertion cycles and off axis insertions.

### Features:

- RADSOK contacts provide increased amperage in smaller package
- 30 Amp through 400 Amp/600 Volt inserts available
- Decreased weight & panel layout compared to the competition
- Double lead Acme threads for easy coupling
- Machined contacts designed for longer life/mating cycles
- RADSOKs allow for lower insertion forces than standard contacts
- Three key design to limit cross-mating
- Machined aluminum dust cap for environmental protection
- Plugs utilize mechanical clamp strain relief
- VFD rated inserts
- U.L. approval pending

## NEPTUNE® PRODUCT SPECIFICATIONS

- Machined aluminum components heat resistant to 750° F
- Titanium colored Anodic plating
- Nickel Silver Alloy plated contacts
- Operating Temperature rated to -67° F to +225° F
- IP 68-8
- Resistant to 60 G's; Vibration exceeds Mil-STD-167-1



NEPTUNE® inserts utilize RADSOK® patented socket contact design

## NEPTUNE CODE LOGIC

		Receptacle Part Number	Mating Plug Part Number	Min/Max Wire Size
30amps	2p3w	NR-3023	NP-3023	#10-#14
	3p3w	NR-3033	NP-3033	#10-#14
	3p4w	NR-3034	NP-3034	#10-#14
	4p4w	NR-3044	NP-3044	#10-#14
60 amps	2p3w	NR-6023	NP-6023	#4-#8
	3p3w	NR-6033	NP-6033	#4-#8
	3p4w	NR-6034	NP-6034	#4-#8
	4p4w	NR-6044	NP-6044	#4-#8
100 amps	3p4w	NR-10034	NP-10034	1/0-#2
	4p4w	NR-10044	NP-10044	1/0-#2
150 amps	3p4w	NR-15034	NP-15034	1/0-#2
	4p4w	NR-15044	NP-15044	1/0-#2
200 amps	3p4w	NR-20034	NP-20034	4/0-2/0
	4p4w	NR-20044	NP-20044	4/0-2/0

All receptacles are supplied with threaded environmental dust cap

All plugs are supplied with mechanical clamp backshell and sealing grommets

All plugs are supplied less cover, however, are available as separate component

### Markets:

- Oil Exploration Equipment
- Convention Center Power Distribution
- Geophysical Trucks and Skids
- Portable Power Distribution Equipment
- Production Platforms
- Communication Shelters

### Additional catalogs of interest:

- Star-line® & Star-line EX® Harsh Environment Connectors, please ask for Catalog 12-054
- Amphe-Power® family of connectors with RADSOK® Technology, please ask for Catalog SL-391

The information contained in this data sheet is for reference only.

Notice: Specifications are subject to change without notice. Contact your nearest Amphenol Corporation Sales Office for the latest specifications. All statements, information and data given herein are believed to be accurate and reliable but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suggestions concerning possible use of our products are made without representation or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should assume that all safety measures are indicated or that other measures may not be required. Specifications are typical and may not apply to all connectors. AMPHENOL is a registered trademark of Amphenol Corporation.

For further information on your individual application requirements, contact: Amphenol Corporation

North America:  
Amphenol Industrial Operations  
180 N. Freeport Drive, Plant 4  
Nogales, AZ 85621  
Tel: (520) 285-5130  
Fax: (520) 285-5134

Email: [rpedrzzini@amphenol-aio.com](mailto:rpedrzzini@amphenol-aio.com)

Europe:  
Amphenol Industrial Operations Europe  
Via Barbaiana 5  
1-20020 Lainate (MI) Italy  
Tel: +39 02 93254.204  
Fax: +39 02 93254.444

Email: [info@amphenol-aio.com](mailto:info@amphenol-aio.com)

Middle East:  
Amphenol Middle East Enterprises FZE  
Office C-37 PO Box 21107  
Ajman Free Zone, UAE  
Tel: +9716-7422494  
Fax: +9716-7422941

Email: [ameefze@eim.ae](mailto:ameefze@eim.ae)

Asia:  
Amphenol Technology Shenzhen Ltd  
Block 5 Fuan 2nd Industrial Park  
Dayang Rd, Fuyong Baoan  
Baoan, Shenzhen, China 518103  
Tel: +86 755 2881 8389  
Fax: +86 755 2991 8310  
Email: [yb.zhu@amphenol-industrial.com](mailto:yb.zhu@amphenol-industrial.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[NR-6044](#) [NR-10044](#) [NR-20044](#) [NP-3034](#) [NP-3044](#) [NP-6034](#) [NP-3023](#) [NP-3033](#) [NP-10034](#) [NP-10044](#) [NP-15044](#)  
[NP-20034](#) [NP-6044](#) [NP-15034](#) [NP-20044](#) [NR-15044](#)