

| | | | | | | | | |
|---|---|---|---|--------|-------------------------|-----------------|-------------|------------------------------|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | |
| | | | | REV. A | ECN NO. Initial Release | DATE 2010/04/22 | SIGN Jessie | DESCRIPTION Form Rev.02 To A |
| | | | | | | | | |
| | | | | | | | | |

1

2

1

2

72.5(REF.)

27.7(REF.)

⑦ Cable Cover

⑧ Screw

③④⑤ Seal

⑥ Sealing Nut

② Body

① Half-Finished Goods

ALTW
DCC. DEPT.
CONFIDENTIAL
2010.04.22
R&D DEPT.

ALTW
DCC. DEPT.
CONFIDENTIAL
2010.06.09
ISSUED

Note:

- * @@Important Dimension
- * Waterproof Rate: IP68
IP68: 1M depth of water in 24 Hrs.
(防水等級：IP68)
IP68：水深一米測試 24 小時
- * Cable OD: ø5.5mm~ø12.5mm
- * Gasket: Silicone ,Gray
- * Shell: Zinc Alloy ,Electrodeposition Coating,Black.
- * Male Pin: Copper Alloy ,Gold Plated
- * Insulation: Nylon ,Black
- ⑨* One Set Assembled in one PE Bag.

| | | | | | | | | |
|---|--|--|-----------------|-------------------------------|--|-------------------------------|---------------------|--------------------|
| UNIT:mm | | TITLE Circular II Series 2 Pin Assy | | Amphenol LTW 安費諾亮泰企業股份有限公司 | | ITEM NO HC20-02BFMA-SL8001 | DRAWN BY Jessie | DATE 2010/04/22 |
| TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1° | | SCALE Free | SHEET 1 OF 1 | | | DWG NO HC20-02BFMA-SL8001 | CHECKED BY Jimmy | DATE 2010/05/12 |
| | | REV. A | SIZE A4 | QC :Inspection Item | | CUSTOMER ALTW | APPROVED BY Win | DATE 2010/05/12 |

1

2

3

4

5

6

7

8 FMWIO702-01-01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HC20-02BFMA-SL8001](#)