




REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	--	FIRST RELEASED	APR-10-2020	BLINK	TOMMY



NOTES: (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL:

SHELL: THERMOPLASTIC, UL94 V-0.

2. SPECIFICATIONS:

- 2.1, OPERATING TEMPERATURE: -40~125°C.  
2.2, MATING CYCLES DURABILITY: 100 CYCLES MIN (MATING WITH PL000733)  
2.3, RoHS COMPLIANT.

3. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

TITLE:	TELECOM 2.4mm CONNECTOR PLUG HOUSING
DWG NO:	PL000734
REV:	A1
SH:	1
OF:	1

QUANTITY	PART NUMBER	DESCRIPTION		ITEM
MATERIALS LIST				
<div>UNLESS OTHERWISE SPECIFIED</div> <div>1) All dimensions are in metric(mm).</div> <div>2) Tolerances are as follows:</div> <div><div>1 PL DEC ±0.30</div><div>2 PL DEC ±0.15</div><div>3 PL DEC ±0.08</div></div> <div>Fractions ±1/64</div> <div>Angles ±1°</div> <div>3) Note reference = </div>		<div>SIGNATURES</div> <div>DRAWN: BLINK</div> <div>CHECKED: ORION</div> <div>ENGINEER:</div> <div>APPROVAL: TOMMY</div> <div>CUSTOMER:</div> <div>THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.</div>	<div>DATE</div> <div>APR-10-2020</div> <div>APR-13-2020</div> <div></div> <div>APR-15-2020</div>	<div>Amphenol</div> <div>Sine Systems - <a href="http://www.amphenol-sine.com">www.amphenol-sine.com</a></div> <div>44724 Morley Drive</div> <div>Clinton Township, MI 48036</div> <div>2.4MM FEMALE PLUG HOUSING</div> <div>FOR USE WITH PL000735, PRM SERIES™</div> <div><div>SIZE</div><div>B</div><div>TYPE</div><div>C-</div><div>DWG NO:</div><div>PL000734</div><div>REVISION</div><div>A1</div></div> <div><div>SCALE:</div><div>NONE</div><div>SHEET 1 OF 1</div></div>
MATERIAL SPECIFICATIONS:				
PROCESS SPECIFICATIONS:				
NEXT ASSY:				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PL000734](#)