





REVISIONS				
REV	ECO	DESCRIPTION	DATE	BY APPR
A1	-	RELEASED DRAWING	Nov-8-17	Rookie Tommy
A2	-	ADD THE G5 PART NUMBER	Jan-28-19	Blink Tommy
A3	-	CHANGE HAND CRIMPER	Nov-8-19	Flan Tommy



CONTACT ORIENTATION ON ROLL
NOTES: (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL:
 - 1.1. CONTACT BODY: COPPER ALLOY.
 - 1.2. OUTER SPRING: STAINLESS STEEL.
2. SPECIFICATIONS:
 - 2.1 CURRENT RATING: 5A MAX.
 - 2.2 TERMINATION TYPE: CRIMPING.
 - 2.3 WIRE RANGE: 26~24AWG.
 - 2.4 WIRE INSULATION DIA(MAX): Ø2.2mm.
3. RoHS COMPLIANT.
4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
5. AVAILABLE TOOLS:
 - 5.1 HAND CRIMPER: MFX-3958. A3
 - 5.2 CRIMP APPLICATOR: MFX-3957.
 - 5.3 EXTRACTION TOOL: QXRT20.



SECTION B-B

P/N	CONTACT PLATING(MATING AREA)
SS24W2T	TIN PLATING OVER NICKEL.
SS24W2N	NICKEL PLATING OVER COPPERIZE.
SS24W2F	GOLD FLASH PLATING OVER NICKEL.
SS24W2G5	5µ" GOLD PLATING OVER NICKEL.
SS24W2G10	10µ" GOLD PLATING OVER NICKEL.
SS24W2G15	15µ" GOLD PLATING OVER NICKEL.
SS24W2G30	30µ" GOLD PLATING OVER NICKEL.

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED			
1) All dimensions are in millimeters.			
2) Tolerances are as follows:			
1 Pt. DEC 40.20			
2 Pt. DEC 40.20			
3 Pt. DEC 20.08			
3) Note reference = A3			
MATERIAL SPECIFICATIONS			
CUSTOMER: Tommy			
APPROVE: Tommy			
NOV-8-19			
PROCESS SPECIFICATIONS			
THE DRAWING IS SUPPLIED FOR INFORMATION ONLY. IT DOES NOT REPRESENT THE MANUFACTURING PROCESS. SPECIFICATIONS AND PERFORMANCE DATA ARE FOR REFERENCE ONLY. THE MANUFACTURING CORPORATION NO RIGHTS OF REPRODUCTION ARE GRANTED. ALL DIMENSIONS ARE IN MILLIMETERS. MANUFACTURING VARIATIONS			
NEXT ASBY			
SCALE: NONE			
SHEET 1 OF 1			

Amphenol

Sine Systems - www.amphenol-sine.com
44724 Money Drive
Clinton Township, MI 48038

ECO-MATE SOCKET CONTACT,
STAMPED, 24-26AWG, SIZE 20

SIZE	TYPE	SS24W2XX	REVISION
B	C-		A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SS24W2G30](#)