



NOTES:

1. PACKAGE CABLE ASSEMBLY IN BAG. TAG IN BAG WITH "AMPHENOL CONNEX, 336209-12-XXXX AND DATE CODE".
2. CABLE ASSEMBLY TO BE 100% TESTED FOR CONTINUITY, SHORTS AND OPEN.

336209-12-XXXX		REVISIONS			
DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	A	RELEASE TO MFG.	08-Feb-11	--	RAK



LENGTH TABLE		
CONNEX NUMBER	CABLE LENGTH (IN)	CABLE LENGTH (MM)
336209-12-0050	1.968 ±0.150"	50 ±3.81
336209-12-0100	3.936 ±0.150"	100 ±3.81
336209-12-0150	5.905 ±0.150"	150 ±3.81
336209-12-0200	7.873 ±0.200"	200 ±5.08
336209-12-0250	9.842 ±0.200"	250 ±5.08
336209-12-0300	11.810 ±0.200"	300 ±5.08

* ADDITIONAL LENGTHS CAN BE PROVIDED BY CHANGING XX.XX TO DESIRED LEGNTH IN MM CONTACT CONNEX MARKETING FOR QUOTE

DESIGN REQUIREMENTS:

<input type="checkbox"/> FREQUENCY _____ TO _____ GHz	<input checked="" type="checkbox"/> CONTINUITY
<input type="checkbox"/> VSWR _____ : 1 MAX	<input checked="" type="checkbox"/> HI-POT :200 VRMS
<input type="checkbox"/> INS. LOSS _____ dB MAX	<input type="checkbox"/> OTHER

100901-02	1	3	MICRO COAX PLUG TERMINATED TO 1.13 MM	
009-954-458	A/R	2	HEAT SHRINK TUBE	
122542	1	1	TNC BLKHD CRIMP JACK, IP 67	
PART NUMBER	QTY	ITEM	DESCRIPTION	FINISH

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL ±.015 (0,381 mm) 3 PLACE DECIMAL ±.005 (0,127 mm) ANGLES ± 1°	MATERIAL	DRAWN ABHAYA KISHORE	DATE 08-Feb-11	TITLE TNC BLKHD CRIMP JACK, IP67 TO MICRO COAX PLUG TERMINATED, USING 1.13MM CABLE, XXXX MM, LENGTH	Amphenol Connex
	REFERENCE TASK - 563	ENGINEER ABHAYA KISHORE	DATE 08-Feb-11		
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.		APPROVED	DATE		SCALE: 4.0:1
			CAD FILE Root folder:/Cable assembly/336209-12-XXXX	DWG SIZE B	DRAWING NO. 336209-12-XXXX
					REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[336209-12-0050](#) [336209-12-0100](#) [336209-12-0150](#) [336209-12-0200](#) [336209-12-0250](#) [336209-12-0300](#)