	1 2	3	5 6 7
			SIGN DATE DESCRIPTION APPROVER
		Dim P	A 04/07'10 Add the 2P mark Runner
		7.50	▲ 09/20'10 Layout of Hook and Pillar & Current rating is changed Runner
			▲ 05/09'11 The dimensions is Changed from 26.3 &14.5 to 26.5 &14.7 Chen Bo
E			▲ 08/22'12 Update the drawing Da cheng
			THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!
		│ └╶╶ <u>┤</u> ╶┼ <u>╱</u> ╎ ╲╏ ┼ <u></u> ┎┷ <u></u> <mark>┤</mark> ┎┷ <mark>┙</mark>	Material:
			 Item 1 Female contact :PhBz Tin plated
			Item 2 Spring Clamp: Stainless steel
			 Item 3 Terminal housing (With hook) :Thermoplastic (UL94V-0)
			Item 4 Terminal housing (With Pillar) :Thermoplastic (UL94V-0)
	\bigcirc	Dim L ► NC/	 Item 5 Terminal (cover):Thermoplastic (UL94V-0)
	J	V	Item 6 Pad board: Thermoplastic (UL94V-0)
D		Hook Pillar Pillar Hook Pillar	
		Hook Pillar Pillar Hook Pillar	Electrical: cULus
			☐ ↓ Voltage rating: 300 V
		# // #	A ● Current rating: 8 A
			│
\mathbf{H}			Solid wire(AWG): 12-28
			■ Stranded wire(AWG) 12-28
			● Wire strip length: 8–9 mm
l r			● Operating temperature: -40°C to +115°C
			• Critical dimension: 🗸
			▲ HI xx 2 0 x 0 xxxx G
			POLES RoHS compliant
	14.7	Dim B	02: 2pole (lead<4%) 🛆
			In copper Alloy
	V <u>~</u>		16: 16pole 0000: "@" Logo (Standard)
В			5: GREEN Any special item by 6: BLUE customer requst.
			8: GREY please contact sales
			department.
		2.6	
\square	^		
	\triangle		ANYTEK CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE
	Layout of Hook and Pillar:	TOL	
	2P Hook+Pillar	DIM 2P-4P 5P-8P 9P-12P	PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD
	3P Hook+Hook+Pillar		±0.40 TITLE HI 7.5mm Without flange Series
	4P Hook+Pillar+Hook+Pillar	Dim L N×7.5-2.5 ±0.15 ±0.25 ±0.30	PART NO. HIxx20x0xxxxG DWG NO. 8HI0101
A	5P Hook+Pillar+Pillar+Hook+Pillar	Dim P (N-1)×7.5 ±0.15 ±0.25 ±0.30	±0.40
	5P over Hook+Pillar+ ^{pillar} +Pillar+Hook+Pillar		ATTROVED CHECKED DESIGNED DRAWN COST NO. X. ±0.50
		Dim B N×7.5-0.9 ±0.15 ±0.25 ±0.30	
			Dacheng Dacheng Call: NONE X.XX ±0.10 2012.08.22 2012.08.22 SHEET: 01/01 REV.: F X° ±1°
	1 2	3	5 6 7
	I 4		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

 HI0220500000G
 HI0320500000G
 HI0420500000G
 HI0520500000G
 HI0620500000G
 HI0720500000G

 HI0820500000G
 HI0920500000G
 HI1020500000G
 HI1120500000G
 HI1220500000G
 HI1320500000G

 HI14205000000G
 HI1520500000G
 HI1620500000G
 HI1220500000G
 HI1320500000G