

NOTES:



- MATERIALS AND FINISHES(PLATING THICKNESS IN MICRO-INCHES):
BODY - BRASS, NICKEL PLATING
CONTACT - BERYLLIUM COPPER, GOLD PLATING
INSULATOR - PTFE
- ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC 0-1 GHz
C. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.
- MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: - 65°C to +165°C

THIRD ANGLE PROJ.





REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	07-Jan-04	44588	TOM
B	REDRAWN TO UPADTE FORMAT	02-May-08	47064	SHE



PCB MOUNTING HOLE



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

REFERENCE

FINISH

DRAWN

S.XIE

ENGINEER

S.XIE

APPROVED

TOM

CAD FILE

F:\DWG\MNB\6252A1\005\75\NT30G-BSZ

DATE

07-Jan-04

DATE

07-Jan-04

DATE

07-Jan-04

TITLE

MINI BNC R/A PCB
MOUNT JACK

SCALE: 3/1

DWG SIZE

B

CODE ID

74868

SHEET

2 OF 2

REV

B

Amphenol RF

Danbury CT USA, Tainan Taiwan, Shenzhen China
www.amphenolrf.com

DRAWING NO. MNB6252A1-005-NT30G-75

ITEM NO. 316252AAE36NC7F

PART NO. 031-70265

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[031-70265](#)