


PT02 SE (MS3122)

SP02 SE

box mounting receptacle



PT02SE-XX-XXX
 SP02SE-XX-XXX
 MS3122E-XX-XXX

To complete part number see how to order on page 36.
 ■ (MMC) located within .0025 of (TP)

Shell Size	Receptacle Front View						Receptacle Side View							
	R		S Max.		T Dia. ±.005		A Dia. +.001 −.005	D Max.		K ±.016	L Max.	M +.010 −.000		N Dia. +.011 −.000
	PT	SP	PT	SP	PT	SP		PT	SP			PT	SP	
8	.594	—	.828	—	.120	—	.473	.312	—	.062	1.296	.431	—	.438
10	.719	.812	.954	1.141	.120	.150	.590	.312	.219	.062	1.296	.431	.462	.562
12	.812	.938	1.047	1.266	.120	.150	.750	.312	.219	.062	1.296	.431	.462	.688
14	.906	1.031	1.141	1.360	.120	.150	.875	.312	.219	.062	1.296	.431	.462	.812
16	.969	1.125	1.234	1.453	.120	.150	1.000	.312	.219	.062	1.296	.431	.462	.938
18	1.062	1.203	1.328	1.532	.120	.150	1.125	.312	.219	.062	1.296	.431	.462	1.062
20	1.156	1.297	1.453	1.688	.120	.150	1.250	.406	.344	.094	1.358	.556	.556	1.188
22	1.250	1.375	1.578	1.766	.120	.150	1.375	.406	.344	.094	1.358	.556	.556	1.312
24	1.375	1.500	1.703	1.891	.147	.150	1.500	.406	.344	.094	1.358	.589	.589	1.438

All dimensions for reference only.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[PT02SE-10-6S\(SR\)](#) [PT02SE-12-3P\(SR\)](#) [PT02SE-12-3S\(SR\)](#) [PT02SE-12-8S\(SR\)](#) [PT02SE-14-12S\(SR\)](#) [PT02SE-14-18P\(SR\)](#) [PT02SE-14-18S\(SR\)](#) [PT02SE-14-19P\(SR\)](#) [PT02SE-14-19S\(SR\)](#) [PT02SE-18-30P\(SR\)](#) [PT02SE-18-32S\(SR\)](#) [PT02SE-20-39P\(SR\)](#) [PT02SE-22-25S\(SR\)](#) [PT02SE-24-61P\(SR\)](#) [PT02SE-24-61S\(SR\)](#)