



NOTES:

1. PACKAGE CABLE ASSEMBLY IN BAG. TAG IN BAG WITH "AMPHENOL CONNEX, 336503-13-XXXX AND DATE CODE".
2. CABLE ASSEMBLY TO BE 100% TESTED FOR CONTINUITY, SHORTS AND OPEN.

336503-13-XXXX		REVISIONS			
DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	A	RELEASE TO MFG.	21-Apr-11	--	RAK



CONNEX NUMBER	CABLE LENGTH (IN)	CABLE LENGTH (MM)
336503-13-0050	1.968 ±0.150	50 ±3.81
336503-13-0100	3.936 ±0.150	100 ±3.81
336503-13-0150	5.905 ±0.150	150 ±3.81
336503-13-0200	7.873 ±0.200	200 ±5.08
336503-13-0250	9.842 ±0.200	250 ±5.08
336503-13-0300	11.810 ±0.200	300 ±5.08

* ADDITIONAL LENGTHS CAN BE PROVIDED BY CHANGING XXXX TO DESIRED LENGTH IN MM CONTACT CONNEX MARKETING FOR QUOTE

DESIGN REQUIREMENTS:

- | | |
|---|--|
| <input type="checkbox"/> FREQUENCY _____ TO _____ GHz | <input checked="" type="checkbox"/> CONTINUITY |
| <input type="checkbox"/> VSWR _____ : 1 MAX | <input checked="" type="checkbox"/> HI-POT :200 VRMS |
| <input type="checkbox"/> INS. LOSS _____ dB MAX | <input type="checkbox"/> OTHER |

PART NUMBER	QTY	ITEM	DESCRIPTION	FINISH
100910-01	1	3	MICRO COAX R/A PLUG TERMINATED TO 1.32 MM CABLE	
009-954-458	A/R	2	HEAT SHRINK TUBE	
252200	1	1	MCX STR BHD CRIMP JACK	

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:
 2 PLACE DECIMAL ±.015 (0,381 mm) 3 PLACE DECIMAL ±.005 (0,127 mm) ANGLES ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

REFERENCE
TASK - 613

DRAWN
ABHAYA KISHORE

ENGINEER
ABHAYA KISHORE

APPROVED

CAD FILE
Root folder:\Cable assembly\336503-13-XXXX

DATE
21-Apr-11

DATE
21-Apr-11

DATE

TITLE
MCX STR BHD CRIMP JACK TO
MICRO COAX R/A PLUG TERMINATED
TO 1.32MM CABLE
XXXX MM,LENGTH

Amphenol
Connex

SCALE: 5.0:1 SHEET 1 OF 1

DWG SIZE DRAWING NO. REV
B 336503-13-XXXX A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[336503-13-0050](#) [336503-13-0100](#) [336503-13-0150](#) [336503-13-0200](#) [336503-13-0250](#) [336503-13-0300](#)