









NOTES:	35025-RFX		REVISIONS				
	DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR	
	THIRD ANGLE PROJ.		--	RELEASE TO MFG.	-----	-----	----
		B	SEE SHEET 1	10/23/03	44666	CPM	
<div><div><div><div>1. MATERIALS OF CONSTRUCTION: HOUSING, BODY, BRAID CLAMP & HEX NUT = BRASS (ASTM-B16 H02, C36000), NICKEL PLATED (.000100 MIN THICK) CONTACT PIN = PHOSPHOR BRONZE (QQ-B-750), GOLD PLATED (.000003 MIN THICK) WASHER = BRASS (QQ-B-613), NICKEL PLATED (.000100 MIN THICK) INSULATOR = PTFE PER ASTM D 1710 OR EQUIV. GASKET = SILICONE RUBBER, COLOR RED</div><div>2. CRIMPED CONTACT PIN = HEX CRIMP SIZE .100</div><div>3. ELECTRICAL: A. IMPEDANCE: 50 OHM B. FREQUENCY RANGE: DC - 11 GHz C. DIELECTRIC WITHSTANDING VOLTAGE: 2,500 VRMS, MIN.</div><div>4. MECHANICAL: A. TEMPERATURE RANGE: -65° C TO +165° C</div><div>5. PACKAGING: A. QUANTITY: SINGLE PACK B. MARKING: BAG TO BE MARKED "AMPHENOL, 35025-RFX, AND DATE CODE"</div></div><div><p>SCALE 1.000</p></div></div></div>							
<div><div><p>RECOMMENDED CABLE STRIPPING DIMENSIONS SCALE 3.000</p></div></div>							
<div><div><div><div><div>CUSTOMER OUTLINE DRAWING</div><div>ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY</div></div></div></div></div>							
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MM (INCHES) AND TOLERANCES ARE: 0.5 - 6mm ±0.2mm 6 - 30mm ±0.4mm 30 - 120mm ± 0.6mm		MATERIAL		DRAWN C. McGRATH	DATE 21-Nov-00	TITLE N CLAMP SOLDER JACK FOR RG-58C/U, 58/U, 142A/U, 223/U CABLES	Amphenol Amphenol Corporation Communication and Network Products Division Danbury, CT U.S.A. 06810
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.		REFERENCE GEN# 34525-RFX_ASSY EAR 962370		ENGINEER O. BARTHELMES	DATE 21-Nov-00		
				APPROVED O. BARTHELMES	DATE 21-Nov-00		SCALE: 2.0:1
				CAD FILE I:\N\35025-RFX		CODE ID 74868	DWG SIZE B
						DRAWING NO. 35025-RFX	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[000-35025-RFX](#)