



NOTE: 1. FOR EXAMPLE: FOR AN EP-8-11P USE ASSY No. 128199-0008

EP-* - 11P TYPE	EP/AP INSERT P/N
EP - 2 - 11P	156-4401-002
EP - 3 - 11P	156-4401-003
EP - 4 - 11P	156-4401-004
EP - 5 - 11P	156-4401-005
EP - 6 - 11P	156-4401-006
EP - 8 - 11P	156-4401-008

ITEM	PART No.	DWG No.	DESCRIPTION	QTY
7	012-4026-00*	012-4026-00*	EP BUSHING	1
6	026-4016-000	026-4016-000	EP 11 & 12 CLAMP	1
5	990-4094-000	990-4094-000	CABLE CLAMP SCREW FOR EP	2
4	990-4400-000	990-4400-000	2-32 PAN HEAD SCREW	1
3	248-4108-000	248-4108-000	EP 11 SHELL, LONG VERSION	1
2	011-4400-000	011-4400-000	EP BARREL	1
1	SEE CHART	SEE CHART	EP SOCKET INSULATOR ASSY	1

UNLESS OTHERWISE SPECIFIED
TOLERANCE TO BE:
LINEAR: X ± 0.5, X' ± 1', X.X ± 0.1, X'X' ± 30', X.XX ± 0.05, X'X'X' ± 15'
ANGULAR: X' ± 1', X'X' ± 30', X'X'X' ± 15'

BREAK ALL SHARP EDGES AND REMOVE ALL BURRS
DO NOT SCALE

DIMENSIONS IN MILLIMETRES

THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD.. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER

CAD FILE: 00805100
DRN: S.M.D
DATE: 07-02-90
MATERIAL: REFER TO COMPONENT
FINISH: REFER TO COMPONENT

SCALE: 2:1 UOS

1	UPDATE TO AMPHENOL TITLE BLOCK & LOGO REDRAW & ADD BOM	M.N.H.	12-04-01	7783
<input checked="" type="checkbox"/>	FIRST ISSUE	S.M.D	07-02-90	----
REV.	CHANGE DETAILS	BY	DATE	CHG/No
TITLE: EP-* - 11P CUSTOMER/ASSEMBLY DRAWING		Amphenol Amphenol Australia Pty Ltd, 2 Fineways Blvd, Keaysborough, Vic 3173 DRAWING NO. 128199-000* SHEET 1 of 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[EP-6-11P](#) [EP-6-11PB](#)