

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	DCN 46701	08/17	GPF

MATERIAL:

CONNECTORS:

CABLE:

SHRINK TUBING:

PERFORMANCE:

IMPEDANCE:

FREQ. RANGE:

SEE NOTES

SEE NOTES



STANDARD FLEXTRA CABLE (200-70-214)

M23053/5

50 OHMS

DC TO 18.0 GHZ

SV P/N	L (OAL)
7029-2558	6.000"
7029-2559	12.000"
7029-2560	24.000"

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63 MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	<div><p>2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409</p></div> <div>TITLE: SMA FEMALE TO SMPM FEMALE FOR .047 CABLE ASSEMBLY</div>
FINISH:	SEE NOTES	FRACTIONAL: ± 1/64 ANGULAR: X° ± 1°0' X°X' ± 15'		
SURFACE AREA:	N/A	DECIMAL: .X ± .030 .XX ± .010 .XXX ± .005		
PROPRIETARY		INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994		
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		THIRD ANGLE PROJECTION	DRAWN: VB 08/04/17	SIZE: B CAGE CODE: 95077 DWG. NO. 7029-2558-2560
			CHECKED: GPF 08/04/17	SCALE: 1:1
			APPROVED: GPF 08/04/17	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7029-2558](#) [7029-2559](#) [7029-2560](#)