


NOTES:

1. MATERIALS AND FINISHES:
 - BNC JACK:
 - BODY - BRASS, NICKEL PLATING
 - CONTACT - BeCu, GOLD PLATING
 - INSULATOR - PTFE, NATURAL
 - MMCX PLUG:
 - BODY & CONTACT - BRASS, GOLD PLATING
 - INSULATOR - PTFE, NATURAL
 - CABLE - RG-316
2. ELECTRICAL:
 - A. IMPEDANCE: 50 OHM
3. PACKAGING:
 - A. QUANTITY: SINGLE PACK
 - B. MARKING: BAG TO BE MARKED
"AMPHENOL, 95-850-207-XXX, AND DATE CODE"

THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECN	APPR
A	RELEASE TO MFG.	02-Oct-18	09322	SV



95-850-207-048	48.00 [1.219]	1.50 [0.038]
95-850-207-036	36.00 [0.914]	
95-850-207-024	24.00 [0.610]	
95-850-207-012	12.00 [0.305]	0.75 [0.019]
95-850-207-006	6.00 [0.152]	
PART NUMBER (IMPERIAL)	LENGTH 'L' IN INCHES [METERS]	LENGTH 'X' INCHES [METERS] MIN

24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
LENGTH IN INCHES/FT [METERS]	TOLERANCE
TOLERANCE TABLE	

DESIGN REQUIREMENTS

- FREQUENCY: DC TO 4 GHz CONTINUITY
 VSWR: ---- :1 MAX HI-POT: 500 VRMS
 INS. LOSS: ---- dB MAX OTHER

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
 <0.5mm ±0.05mm 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL SEE NOTES	DRAWN S.VO	DATE 12-Jun-18
REFERENCE EAR# 8326	ENGINEER S.VO	DATE 12-Jun-18
REF: ---	APPROVED ---	DATE ---
CONFIGURATION LEVEL: In Work	CAD FILE	
FINISH		

TITLE BNC BHD JACK TO MMCX R/A PLUG ON RG-316 CABLE	DWG SIZE B	REV A
--	---------------	----------

SCALE: 2.0:1.0	SHEET 2 OF 2
----------------	--------------

Amphenol RF	
www.amphenolrf.com	
DRAWING NO.	95-850-207-XXX
ITEM NO.	95-850-207-XXX
PART NO.	95-850-207-XXX

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[095-850-207-006](#) [095-850-207-024](#) [095-850-207-048](#)