

1	2	3	4	5	6	7	8
				REV. B	ECN NO. LE31110020~024	DATE 2011/01/05	SIGN Vicky
				C	LEN1640377~382	2016/04/13	Ruru
							DESCRIPTION Mini Size Molding外觀變更
							Change Logo

ALTW
CONFIDENTIAL
2016.04.13
R&D DEPT.

ALTW
DCC. DEPT.
CONFIDENTIAL
2016.05.04
ISSUED

Pin Assignments
Front View

3	Black	黑
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		

AD-03BFFM-LL7000
Color:Black

AD-03BFFM-LL7AXX

XX:01~99Meter
01:01Meter
02:02Meters
:
99:99Meters

Cable Length(L):01~99Meters

Note:
* @@Important Dimension.
* Waterproof Rate:IP67.
* Connector:Nylon+GF,Black.
* Female Pin:Copper Alloy,Gold Plated.
* Lock Nut:Nylon+GF,Black.
* O-Ring:EPDM,Black.
* Cable:UL2464 24AWG*3C+D+A,Black, PVC Jacket,UV Resistant,OD=4.5mm.
* Cable Length Tolerance:01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE
TOLERANCE		Mini,Cable Lock 3P F Conn F Pin
±0.5 mm		

SCALE	Free	SHEET 1 OF 1
REV. C	SIZE A4	QC :Inspection Item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2016/04/13
DWG NO AD-03BFFM-LL7AXX	CHECKED BY Rita	DATE 2016/04/13
CUSTOMER ALTW	APPROVED BY Lisa	DATE 2016/04/13

8 FMWIO702-01-01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AD-03BFFM-LL7A02](#) [AD-03BFFM-LL7A05](#) [AD-03BFFM-LL7A01](#) [AD-03BFFM-LL7A10](#) [1AD-03BFFM-LL7A01](#)