

1	2	3	4	5	6	7	8	
				REV.	ECN NO.	DATE	SIGN	DESCRIPTION
				B	LEN-860098~101	2008/05/10	Zhang Jin	Change 42.5 To 42.7.
				C	LEN-920244~247	2009/02/04	Vicky	Update the drawing.
				D	LEN1650516~519	2016/05/16	Vicky	Update Logo

8-04AMMM-SL7000 ①
Color:Black

8-04AMMM-SL7AXX
XX:01~99Meters
01:01Meter
02:02Meters
:
:
99:99Meters
Cable Length(L):01~99Meters

ALTW
CONFIDENTIAL
2009.02.06
R&D DEPT.

ALTW
DCC. DEPT.
CONFIDENTIAL
2016.05.24
ISSUED

Note:

- * @C Important Dimension.
- * Waterproof Rate:IP67.
- * Connector:Black,PU.
- * Male Pin:Copper Alloy,Gold Plated.
- * Cable:UL2464 22AWG*4C+Talcum,Black, PVC Jacket,UV Resistant,OD=5.0mm.
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

Pin Assignments
Front View

4	Black	黑
3	Blue	藍
2	White	白
1	Brown	棕
Conn.	Wire Color	
Pin Out		

UNIT:mm		TITLE
TOLERANCE		M8 Conn Cable Screw 4P M Conn M Pin
±0.5 mm		SCALE Free SHEET 1 OF 1
	REV. D	SIZE A4 @C :Inspection Item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
8-04AMMM-SL7AXX	Vicky	2016/05/16
ALTW	Rita	2016/05/16
	Lisa	2016/05/16

1

2

3

4

5

6

7

8 FMW10702-01-01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8-04AMMM-SL7A05](#) [8-04AMMM-SL7A01](#) [8-04AMMM-SL7A02](#) [8-04AMMM-SL7A10](#)