



Article: **10134283-001LF**

Earth Terminal Block - yellowgreen
Screw connection - 6mm² / 8AWG - Width 8 mm



GENERAL DATA

Series	EURO E16-25
Item	10134283
Weight/Piece	56,8 g
Colour	YellowGreen
Q.ty p.pck.	25
Q.ty p. box	250

TECHNICAL DATA / DIMENSIONS

Dimensions

Width mm(in.)	12 (0.47)
Length mm(in.)	58 (2.28)
Height mm(in.)	49 (1.93)
Mounting type (EN 60715)	Omega TH35

Technical data

Maximum load current	-
Insulating material	PA
Self-extinguishing degree acc. to UL94	V2
Rated surge voltage	6kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Nominal Voltage	-
Nominal Current	-
Temperature index, insulating material – Elec. UL 746 B - RTI	130°C
Static insulating material lower permissible temperature	-60°C

Connection data

Conductor cross-section solid min/max	1.5 / 25 mm ²
Conductor cross-section stranded min/max	1.5 / 16 mm ²

AWG min/max	14-4 AWG
Max conductor cross-section stranded with ferrule with plastic sleeve	16 mm ² / L=12mm
Stripping length	max 14 mm
Screw	M5 – Zinc plated steel
Tightening torque	2Nm / 30 LbIn.
Earth Screw	M3,5 – Zinc plated steel
Tightening torque	0.8Nm / 10 LbIn.
Clamp	Zinc plated steel
Metal part	Zinc plated steel

APPROVALS

RINA

EN60947-7-2

25mm²
EN60068-2-11


Salt mist test for 96 hours

ENEL DV27

UL1059
E203985

AWG 14-4

TECHNICAL DRAWINGS



ACCESSORIES

Marking

Item	Description
10134398-001LF	Single-digit marking tag (5 x 3 mm) - white
10134398-002LF ~ 10134398-011LF	Single-digit marking tag (5 x 3 mm) – with marking: 0 ~ 9
10134398-012LF ~ 10134398-036LF	Single-digit marking tag (5 x 3 mm) – with marking: A ~ Z
10134399-001LF	Marking tag adapter – 6 slots for marking tags
10134401-001LF	Marking tags (6 x 12 mm) - white (<i>special marking on request</i>)
10134449-001LF	Tags 6x12mm (39tags x 20cards)

DIN RAIL system - Mounting and Installation material

Item	Description
10134392-001LF	Steel Omega rail TH35/7,5mm - 2mt length
10134393-001LF	Slotted steel Omega rail TH35/7,5mm - 2mt length
10134394-001LF	Steel Omega rail TH35/15mm - 2mt length
10134395-001LF	Slotted steel Omega rail TH35/15mm - 2mt length
10134387-001LF	Angled support bracket
10134389-001LF	EURO STOP – End bracket width 9
10134390-001LF	EURO STOP – End bracket width 6
10134391-001LF	EURO STOP – Snap-on end bracket width 6

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10134283-001LF](#)