

Crimping Tool

- * Both machined contacts, stamped and formed contacts can be crimped.
- * Suited for cable sizes of 2.5mm²/ 14AWG, 4.0mm²/12 AWG, 6.0mm²/10AWG.
- * The die set and locator can be ordered separately.
- * For flexible cable use only.



Crimping Tool

Appearance	Order number ^{*1}	Cable Range	Suitable for type of contacts			
			H4 S&F	H4 CF	UTX S&F	UTX C&F
	H4TC0003	2.5mm ² / 14AWG ;4.0mm ² /12 AWG 6.0mm ² /10AWG	x			
	UTXTC0003	2.5mm ² / 14AWG ;4.0mm ² /12 AWG 6.0mm ² /10AWG			x	
	UTXTC0004	4.0mm ² / 12AWG ;6.0mm ² /10 AWG 10.0mm ² /8AWG		x		x
	UTXTC0005*2	2.5mm ² / 14AWG ;4.0mm ² /12 AWG 6.0mm ² /10AWG		x		x

*1 Die set and locator are included in the crimping tool.

*2 UTXTC0005 is specifically used for cable size of 4.0mm²/12 AWG&6.0mm²/10AWG with Amphenol's H4 and UTX special version of 4&6 mm² Cold Formed contacts.

Individual Parts to be ordered separately

Appearance Locators & Crimping dies	Order number	Designatio	Cable Range	Suitable for type of contacts			
				H4 S&F	H4 CF	UTX S&F	UTX C&F
	H4TP0002	Locator	2.5mm ² / 14AWG ;4.0mm ² /12 AWG 6.0mm ² /10AWG	x			
	UTXTP0002	Locator	2.5mm ² / 14AWG ;4.0mm ² /12 AWG 6.0mm ² /10AWG			x	
	UTXTP0004	Double-Locator	4.0mm ² / 12AWG ;6.0mm ² /10 AWG 10.0mm ² /8AWG		x		x
	UTXTP0003 ^{*3}	Double-Locator	2.5mm ² / 14AWG ;4.0mm ² /12AWG 6.0mm ² /10AWG		x		x
	UTXTD0003	Crimping Die	2.5mm ² / 14AWG ;4.0mm ² /12 AWG 6.0mm ² /10AWG	x		x	
	UTXTD0005	Crimping Die	4.0mm ² / 12AWG ;6.0mm ² /10 AWG 10.0mm ² /8AWG		x		x
	UTXTD0004 ^{*3}	Crimping Die	2.5mm ² / 14AWG ;4.0mm ² /12 AWG 6.0mm ² /10AWG		x		x

*3 Locator UTXTP0003 and crimping die UTXTD0004 is specifically used for cable size of 4.0mm²/12 AWG&6.0mm²/10AWG with Amphenol's H4 and UTX special version of 4&6 mm² Cold Formed contacts.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[UTXTC0003](#) [UTXTC0005](#)