

1	2	3	4	5	6	7	8	
				REV. B	ECN NO. LEN1590365~68	DATE 2015/09/11	SIGN Ruru	DESCRIPTION Change Logo & Note

BD-06BMFM-LL7000 (1)
Color:Black

ALTW
CONFIDENTIAL
2015.09.11
R&D DEPT.

ALTW
DCC. DEPT.
CONFIDENTIAL
2015.10.06
ISSUED

BD-06BMFM-LL7AXX

XX:01~99Meter
01:01Meter
02:02Meters
:
99:99Meters

Cable Length(L):01~99Meters

Note:

- * QC Important Dimension.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Female Pin:Copper Alloy,Gold Plated
- * Cable: UL2464 24#*6C+Drain+Al/My, UV Resistant ,OD=5.8mm, Black
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

Pin Assignments
Front View 前視圖

White	白	6
Red	紅	5
Orange	橙	4
Yellow	黃	3
Green	綠	2
Blue	藍	1
Wire Color		Conn.
Pin Out		

UNIT:mm		TITLE
TOLERANCE		Standard,Cable Lock 6Pin M Conn F Pin
±0.5 mm		
SCALE	Free	SHEET 1 OF 1
REV. B	SIZE A4	QC :Inspection Item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2015/09/11
DWG NO BD-06BMFM-LL7AXX	CHECKED BY Rita	DATE 2015/09/11
CUSTOMER ALTW	APPROVED BY Lion	DATE 2015/09/11

12345678

8 FMWIO702-01-01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-06BMFM-LL7A10](#) [BD-06BMFM-LL7A01](#) [BD-06BMFM-LL7A05](#) [BD-06BMFM-LL7A02](#)