






Characteristics



General Characteristics	Standard	Value
number of contacts		2
termination technique		crimp
wire gauge		16 mm ² (AWG 6)
max. insulation diameter		8,6 mm
flammability	UL 94	V-0
Electrical Characteristics	Standard	Value
rated voltage	IEC 60664-1	1000 V (UL/CSA: 600 V)
pollution degree	IEC 60664-1	3
installation (overvoltage) category	IEC 60664-1	3
material group	IEC 60664-1	2
rated impulse withstand voltage	IEC 60664-1	8 kV
rated current T _{amb} = 40 °C		65 A
current carrying capacity	IEC 60512-5-2	see derating curve
contact resistance	IEC 60512-2-1	≤ 5 mΩ
insulation resistance	IEC 60512-3-1	≥ 10 ¹⁰ Ω
Climatical Characteristics	Standard	Value
climatic category	IEC 60068-1	40 / 125 / 10
upper temperature	IEC 60512-11-9	+125 °C
lower temperature	IEC 60512-11-10	-40 °C
Mechanical Characteristics	Standard	Value
mechanical operation	IEC 60512-9-1	≥500 mating cycles
Materials	Standard	Value
insert		PA-GF
contacts		CuZn (brass)
contact plating		Ag (silver)
color		black

Alle technischen Daten wurden unter Laborbedingungen ermittelt und können im Praxisbetrieb abweichen.
Es handelt sich bei den Angaben weder um Beschaffenheits- noch um Haltbarkeitsgarantien.
All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guarantees ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

Gewicht (errechnet) / Calc WT: 8 g				Zul. Abw./Tolerances : ISO 2768-m		Maßstab / Scale : 2:1 (1:1)		A3	
Prüfmaß / Testdimension						CUSTOMER DRAWING			
Teileindex / Partindexnumber:				DIN / ISO 13715					
Bagatelle change:									
				Gez.	01.09.2017	Stiftmodul 2-Pol pin module 2 pole			
				Drawn	PWOELFFLE				
				Status	Released				
				Gepr.	08.09.2017				
				Checked	MGRIMM	M C146 A02 801 E8			
				Amphenol Tuchel Industrial GmbH					
03	201700257	01.09.2017	PWOLF			Blatt/Sheet 1			
Index	Änderung/Description	Datum/Date	Name			1 Bl.			
						Ers. f. / Replacement for : M-C146 A02 801 E8 Rev.02			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[C146 A02 801 E8](#)