



NOTES:

1. MATERIALS AND FINISHES:
TYPE N BODY - BRASS, NICKEL PLATING
OUTER CONTACT - BeCu, NICKEL PLATING
CONTACT - BeCu, GOLD PLATING
INSULATOR - PTFE, NATURAL
SPRING - STAINLESS STEEL, PASSIVATED
RETAINING RING - BRASS, NICKEL PLATING
GASKET - FLUOROSILICONE, BLACK
2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC - 12 GHz
C. VSWR(RETURN LOSS): -20 dB MIN @ DC - 6 GHz
-15 dB MIN @ 6 - 12 GHz
D. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -40° C TO 85° C
4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: PACKAGING TO BE MARKED
"AMPHENOL RF, AD-NJHDBNCP-1 & DATE CODE
U.S. PATENT NO. 7,553,177"

THIRD ANGLE PROJ.

REVISIONS				
REV	DESCRIPTION	DATE	ECN	APPR
A	RELEASE TO MFG.	24-Mar-20	14742	SV



PROTECTED UNDER U.S. PATENT # 7,553,177

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL SEE NOTES	DRAWN M. ZHANG	DATE 24-Mar-20	TITLE TYPE N JACK TO HD BNC PLUG ADAPTER 75 OHM		Amphenol RF www.amphenolrf.com	
	REFERENCE	ENGINEER S. VO	DATE 18-Nov-19				
	EAR# 9420 REF: ---	APPROVED S. HSIEH	DATE 26-Mar-20			SCALE: 6.0:1.0	SHEET 2 OF 2
	CONFIGURATION LEVEL: In Work	CAD FILE	DWG SIZE B		REV A		DRAWING NO. AD-NJHDBNCP-1
	FINISH						ITEM NO. AD-NJHDBNCP-1
							PART NO. AD-NJHDBNCP-1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AD-NJHDBNCP-1](#)