

1	2	3	4	5	6	7	8																															
F				REV. B C D	ECN NO. LEN-9A0112~115 LEN-0C0106~109 LEN1480503~506	DATE 2009/04/20 2010/11/23 2014/08/19	SIGN Li Xiu Zhi Ivan Vicky	DESCRIPTION Change SR View & Update Note Change 前導角 View Update Logo																														
E																																						
D																																						
C																																						
B																																						
A																																						
				<p>ALTW CONFIDENTIAL 2014-08-19 R&amp;D DEPT.</p>																																		
				<p>Conn. ALTW DCC. DEPT. CONFIDENTIAL 2014.08.25 ISSUED</p>																																		
				<p>Pin Assignments Front View</p> <table border="1"> <thead> <tr> <th>Conn.</th><th>Wire Color</th><th>Pin Out</th></tr> </thead> <tbody> <tr><td>9</td><td>Black</td><td>黑</td></tr> <tr><td>8</td><td>Red</td><td>紅</td></tr> <tr><td>7</td><td>Pink</td><td>粉紅</td></tr> <tr><td>6</td><td>Gray</td><td>灰</td></tr> <tr><td>5</td><td>Yellow</td><td>黃</td></tr> <tr><td>4</td><td>Green</td><td>綠</td></tr> <tr><td>3</td><td>White</td><td>白</td></tr> <tr><td>2</td><td>Blue</td><td>藍</td></tr> <tr><td>1</td><td>Brown</td><td>棕</td></tr> </tbody> </table>					Conn.	Wire Color	Pin Out	9	Black	黑	8	Red	紅	7	Pink	粉紅	6	Gray	灰	5	Yellow	黃	4	Green	綠	3	White	白	2	Blue	藍	1	Brown	棕
Conn.	Wire Color	Pin Out																																				
9	Black	黑																																				
8	Red	紅																																				
7	Pink	粉紅																																				
6	Gray	灰																																				
5	Yellow	黃																																				
4	Green	綠																																				
3	White	白																																				
2	Blue	藍																																				
1	Brown	棕																																				
				<p>CD-09AMFM-LL7AXX</p> <p>XX : 01~99Meters 01 : 01Meter 02 : 02Meters : 99 : 99Meters</p> <p>Cable Length(L): 01~99Meters</p> <p>Note:      * Ø Important Dimension To Check      * Waterproof Rate: IP67      * Housing: Nylon+GF, Black      * Female Pin: Copper Alloy, Gold Plated      * Cable: UL2464 24AWG*9C+Drain+Al/My, Black, PVC Jacket, UV Resistant, OD=6.0 mm      * Cable Length Tolerance: 01M:±40mm      02M~05M:±60mm      06M~10M:±100mm      11M~30M:±200mm      31M~99M:±500mm   </p>																																		
<p>UNIT:mm</p> <p>TOLERANCE ±0.5 mm</p>				<p>TITLE Middle Cable Lock 9Pin M Conn F Pin</p> <p>SCALE 1:1 SIZE A4 SHEET 1 OF 1</p> <p>REV. D WC-REV. A.1 ØC: Inspection item</p> <p>Amphenol LTW 安費諾亮泰企業股份有限公司</p> <table border="1"> <thead> <tr> <th>ITEM NO</th><th>DRAWN BY</th><th>DATE</th></tr> </thead> <tbody> <tr> <td>DWG NO CD-09AMFM-LL7AXX</td><td>Vicky</td><td>2014-08-19</td></tr> <tr> <td>CUSTOMER ALTW</td><td>CHECKED BY Sam</td><td>DATE 2014-08-19</td></tr> <tr> <td></td><td>APPROVED BY Rita</td><td>DATE 2014-08-19</td></tr> </tbody> </table>					ITEM NO	DRAWN BY	DATE	DWG NO CD-09AMFM-LL7AXX	Vicky	2014-08-19	CUSTOMER ALTW	CHECKED BY Sam	DATE 2014-08-19		APPROVED BY Rita	DATE 2014-08-19																		
ITEM NO	DRAWN BY	DATE																																				
DWG NO CD-09AMFM-LL7AXX	Vicky	2014-08-19																																				
CUSTOMER ALTW	CHECKED BY Sam	DATE 2014-08-19																																				
	APPROVED BY Rita	DATE 2014-08-19																																				
				1	2	3	4	5	6	7	8																											

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol](#):

[CD-09AMFM-LL7A10](#) [CD-09AMFM-LL7A01](#) [CD-09AMFM-LL7A05](#) [CD-09AMFM-LL7A02](#) [1CD-09AMFM-LL7A01](#)