

1

2

3

4

5

6

7

8

REV. A

ECN NO.

Initial Release

DATE 2014/06/25

SIGN Tom gu

DESCRIPTION Change Rev.1 To Rev.A

ALTW
DCC. DEPT.
CONFIDENTIAL
2014.09.16
ISSUED

ALTW
CONFIDENTIAL
2014.06.25
R&D DEPT.

(Please See the Condition 1 & 2)
兩螺絲孔無防水功能(需挖盲孔)
6-32UNC*2

壓迫區域 Gasket

Ø14.0±0.1
最小挖孔尺寸,
最大不得超出
Gasket 壓迫區域

17.00

28.80

36.40

16.00

17.20

27.50

Recommended
Panel Cut-Out

① Half-Finished Goods

② Seals(OD7.8~9.3mm)

③ Sealing Nut

6-32UNC*2

27.2

26.0

40.0(Ref.)

46.5

24.0

Condition 1

Condition 2

UNIT:mm

TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE
RJ Ass'y
(After Plug In)

SCALE Free

SHEET 1 OF 1

REV. A

SIZE A4

QC :Inspection Item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO CSF-D14002

DWG NO CSF-D14002

CUSTOMER ALTW

DRAWN BY Tom

CHECKED BY Ludi

APPROVED BY Victor

DATE 2014/06/28

DATE 2014/06/28

DATE 2014/06/28

Note:
* @C Important Dimension.
* Waterproof Rating: IP67
* Cable OD: Ø7.8~Ø9.3mm
* Gasket. Seals:Silicone,Gray.
* O-ring:Silicone,Gray.
* Body&Sealing Nut:PC+PBT,Black.
* Screw & Washer:Stainless Steel,Silver.
* 螺絲與對插板對鎖後,對插板距本體之均勻距離 0.8mm 為達到 IP67 防水狀態
* ①②③ 組裝後放入一個 PE 袋
(Sealing Nut 鎖 2~3 牙即可)

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CSF-D14002](#)