

NOTES:


1. MATERIALS AND FINISHES:
BODY - BRASS, NICKEL PLATING
REAR BODY - BeCu, NICKEL PLATING
CONTACT - BeCu, GOLD PLATING
INSULATORS - PTFE, NATURAL

2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC - 12 GHz
C. RETURN LOSS: -20 dB MIN. @ DC - 6 GHz
-15 dB MIN. @ 6 - 12 GHz
D. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65°C TO +165°C


4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, AD-HDBNJMCP-12G, DATE CODE,
& U.S. PATENT NO. 7,553,117"

THIRD ANGLE PROJ.

REVISIONS				
REV	DESCRIPTION	DATE	ECN	APPR
I	PRELIMINARY RELEASE	10-Oct-19	--	SV



SCALE 3.500



PROTECTED UNDER U.S. PATENT # 7,553,117

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL SEE NOTES	DRAWN S.VO	DATE 10-Oct-19	TITLE HD BNC JACK TO MCX PLUG ADAPTER		Amphenol RF www.amphenolrf.com	
	REFERENCE	ENGINEER S.VO	DATE 10-Oct-19				
	EAR# 9410 REF: APH-HDBNCP-J	APPROVED --	DATE --			SCALE: 14.0:1.0	SHEET 2 OF 2
	CONFIGURATION LEVEL: In Work	CAD FILE	--	DWG SIZE B		REV I	DRAWING NO. AD-HDBNJMCP-12G
	FINISH						ITEM NO. AD-HDBNJMCP-12G
						PART NO. AD-HDBNJMCP-12G	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AD-HDBNJ MCP-12G](#)