

Customer Information Sheet

IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

ORDER CODE:

F11-111XXX42R

No. OF CONTACTS:
020, 040, 060, 080, 100, 120








TABLE 1: DIMENSIONS

No. OF CONTACTS	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'E'
20	15.50	4.50	7.80	11.20	14.00
40	20.50	9.50	12.80	16.20	19.00
60	25.50	14.50	17.80	21.20	24.00
80	30.50	19.50	22.80	26.20	29.00
100	35.50	24.50	27.80	31.20	34.00
120	40.50	29.50	32.80	36.20	39.00

TOLERANCES	
X. = ± 0.30 mm	X.° = $\pm 5.0^\circ$
.X = ± 0.25 mm	.X° = $\pm 3.0^\circ$
.XX = ± 0.15 mm	.XX° = $\pm 2.0^\circ$
.XXX = ± 0.10 mm	.XXX° = $\pm 1.0^\circ$

JD	2	30.08.24	34146
NAME	ISS.	DATE	CN/CO
APPROVED: J.DEAN			
CHECKED: A.BOXALL			
DRAWN: A.BOXALL			

- NOTES:
- SEE COMPONENT SPECIFICATION C057XX (LATEST ISSUE) FOR COMPLETE CONNECTOR SPECIFICATIONS.
 - PART SHOWN IS F11-11106042R, SEE ORDER CODE FOR POSSIBLE CONFIGURATIONS.
 - SEE SHEET 4 FOR TAPE & REEL DETAILS.

HARWIN

www.harwin.com

TOLERANCES
X. = ± 1 mm
X.X = ± 0.50 mm
X.XX = ± 0.20 mm
X.XXX = ± 0.01 mm
ANGLES = $\pm 5^\circ$
UNLESS STATED

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

MATERIAL:

SEE NOTE 1

TITLE:
0.5mm PITCH FEMALE HORIZONTAL FLECTO CONNECTOR SIGNAL+POWER CONTACTS

DRAWING NUMBER:
F11-111XXX42R

SHT
3 OF
4

Customer Information Sheet

IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION



ALL DIMENSIONS IN mm

ORDER CODE:

F11-111XXX42R

No. OF CONTACTS:

020, 040, 060, 080, 100, 120



REEL DIRECTION



ELONGATED SPROCKET HOLES

TABLE 2: DIMENSIONS			
No. OF CONTACTS	DIM 'A'	DIM 'B'	DIM 'C'
20	14.20	28.40	32.00
40	20.20	40.40	44.00
60		40.40	44.00
80	26.20	52.40	56.00
100		52.40	56.00
120	34.20	68.40	72.00

JD	2	30.08.24	34146
NAME	ISS.	DATE	CN/CO
APPROVED: J.DEAN			
CHECKED: A.BOXALL			
DRAWN: A.BOXALL			

NOTES:
4. PRODUCT TAPE AND REELED IN ACCORDANCE WITH EIA-481 STANDARD.
5. CARRIER TAPE MATERIAL: BLACK POLYSTYRENE.
6. NUMBER OF COMPONENTS PER REEL: 400PCS
6. TAPE POCKETS MAY DIFFER VISUALLY FROM DRAWING.

HARWIN
www.harwin.com

TOLERANCES
X. = ± 1 mm
X.X = ± 0.50 mm
X.XX = ± 0.20 mm
X.XXX = ± 0.01 mm
ANGLES = $\pm 5^\circ$
UNLESS STATED

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

MATERIAL:

SEE NOTE 4

TITLE:
0.5mm PITCH FEMALE HORIZONTAL FLECTO CONNECTOR SIGNAL+POWER CONTACTS
DRAWING NUMBER:
F11-111XXX42R
SHT 4 OF 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Harwin:](#)

[F11-11108042R](#) [F11-11112042R](#) [F11-11106042R](#) [F11-11110042R](#) [F11-11102042R](#) [F11-11104042R](#)