

# Customer Information Sheet

DRAWING No.: Z80-280


IF IN DOUBT - ASK

©

NOT TO SCALE






THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



NOTES:

1. FOR INSTRUCTION SPECIFICATIONS SEE INSTRUCTION SHEET IS-25.
2. SPARE TOOL TIPS CAN BE BOUGHT SEPARATELY. SEE TABLE FOR PART NUMBERS.



ITEM NUMBER	DESCRIPTION	PART No.
1	CONTACT INSERTION/EXTRACTION TOOL HOLDER (BODY)	N/A - NOT SOLD SEPARATELY
2	CONTACT INSERTION/EXTRACTION TOOL HOLDER (CAP)	N/A - NOT SOLD SEPARATELY
3	CONTACT INSERTION TOOL (FOR INSULATION UP TO $\varnothing 0.9\text{mm}$ )	Z80-044C
4	CONTACT INSERTION TOOL (FOR INSULATION $\varnothing 0.9$ TO $\varnothing 1.1\text{mm}$ )	Z80-044D
5	FEMALE CONTACT EXTRACTION TOOL (L-TEK & J-TEK)	Z80-044E
6	L-TEK MALE CONTACT EXTRACTION TOOL	Z80-044F
7	J-TEK MALE CONTACT EXTRACTION TOOL	Z80-044G

MGP	9	12.08.21	30758
NAME	ISS.	DATE	CN/CO
APPROVED: MGP			
CHECKED: RA			
DRAWN: N. CODLING			
CUSTOMER REF.:			
ASSEMBLY DRG:			

## HARWIN

www.harwin.com  
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES  
X. =  $\pm 1\text{mm}$   
X.X =  $\pm 0.50\text{mm}$   
X.XX =  $\pm 0.20\text{mm}$   
X.XXX =  $\pm 0.01\text{mm}$   
ANGLES =  $\pm 5^\circ$   
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

S/AREA:

mm<sup>2</sup>

TITLE:

DATAMATE CRIMP CONTACT INSERTION/REMOVAL TOOL KIT

DRAWING NUMBER:

Z80-280

SHT  
2 OF 2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Harwin:](#)

[Z80-280](#) [M80-044](#)