



HEYlock™ Locking IEC Power Cords

Universal C13 to C14 Locking Power Cords - designed for retrofit!

UL Listed (UL 817) and CE Compliant (IEC 60320)

- The only locking IEC 13-14 power cord that locks at both ends.
- Designed for retrofit - plug and play replacement for existing power cords.
- Universally compatible - requires no mating plug or receptacle on the other side of the connection.
- Consult Heyco for IEC 19-20 power cord configurations.

Type	Gauge AWG/ Cond	WIRE Color *	Length *		PART NO.	DESCRIPTION
			Feet	M		
H05	17/3	Black	1.7	0.5	S8000	LPC-C13/C14-17/3-BLK-H05-1.7
			3.3	1.0	S8002	LPC-C13/C14-17/3-BLK-H05-3.3
			5.0	1.5	S8004	LPC-C13/C14-17/3-BLK-H05-5.0
			6.6	2.0	S8006	LPC-C13/C14-17/3-BLK-H05-6.6
			8.3	2.5	S8008	LPC-C13/C14-17/3-BLK-H05-8.3
SJT	16/3	Black	1.7	0.5	S8020	LPC-C13/C14-16/3-BLK-SJT-1.7
			3.3	1.0	S8022	LPC-C13/C14-16/3-BLK-SJT-3.3
			5.0	1.5	S8024	LPC-C13/C14-16/3-BLK-SJT-5.0
			6.6	2.0	S8026	LPC-C13/C14-16/3-BLK-SJT-6.6
SJT	14/3	Black	1.7	0.5	S8030	LPC-C13/C14-14/3-BLK-SJT-1.7
			3.3	1.0	S8032	LPC-C13/C14-14/3-BLK-SJT-3.3
			5.0	1.5	S8034	LPC-C13/C14-14/3-BLK-SJT-5.0
			6.6	2.0	S8036	LPC-C13/C14-14/3-BLK-SJT-6.6

*Custom colors and lengths available, consult Heyco.



Universal C13 to 5-15P Locking Power Cords - designed for retrofit!

UL Listed (UL 817) and CE Compliant (IEC 60320)

- IEC 13 to NEMA 5-15P power cord that locks at the application end.
- Designed for retrofit - plug and play replacement for existing power cords.
- Universally compatible - requires no mating receptacle on the other side of the connection.
- IEC 13 to any International plug configuration available. Consult Heyco.

Type	Gauge AWG/ Cond	WIRE Color *	Length *		PART NO.	DESCRIPTION
			Feet	M		
SJT	18/3	Black	2.0	0.6	S8052	LPC-C13/515P-18/3-BLK-SJT-2.0
			3.0	0.9	S8053	LPC-C13/515P-18/3-BLK-SJT-3.0
			6.0	1.8	S8056	LPC-C13/515P-18/3-BLK-SJT-6.0
SJT	16/3	Black	2.0	0.6	S8062	LPC-C13/515P-16/3-BLK-SJT-2.0
			3.0	0.9	S8063	LPC-C13/515P-16/3-BLK-SJT-3.0
			6.0	1.8	S8066	LPC-C13/515P-16/3-BLK-SJT-6.0
SJT	14/3	Black	2.0	0.6	S8072	LPC-C13/515P-14/3-BLK-SJT-2.0
			3.0	0.9	S8073	LPC-C13/515P-14/3-BLK-SJT-3.0
			6.0	1.8	S8076	LPC-C13/515P-14/3-BLK-SJT-6.0

*Custom colors and lengths available, consult Heyco.

*Quick
Specs*

Materials

Nylon 6/6 and PVC with Plated Copper Alloy Contacts

Certifications



Certified by UL for Compliance with both Canadian and U.S. Requirements under File E471200 (C13/C14)



Certified by UL for Compliance with both Canadian and U.S. Requirements under File E115330 (C13/5-15P)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[S8006](#) [S8063](#) [S8030](#) [S8053](#) [S8004](#) [S8036](#) [S8066](#) [S8072](#) [S8062](#) [S8073](#) [S8000](#) [S8034](#) [S8052](#) [S8056](#) [S8024](#)
[S8022](#) [S8032](#) [S8008](#) [S8026](#) [S8002](#) [S8076](#) [S8020](#)