


## Part number description :

10134309-XXXLF

LF: Lead Free, RoHs compliant, see note

XXX : Color ref or/and version



| PN             | Colour | Version |
|----------------|--------|---------|
| 10134309-001LF | beige  |         |
|                |        |         |
|                |        |         |
|                |        |         |

## TECHNICAL DATA / DIMENSIONS

## Dimensions

|                          |            |
|--------------------------|------------|
| Width mm                 | 41.0       |
| Length mm                | 84.0       |
| Height mm                | 52.0       |
| Mounting type (EN 60715) | Omega TH35 |

## Technical data

|                                        |       |
|----------------------------------------|-------|
| Maximum load current                   | 232A  |
| Insulating material                    | PA    |
| Self-extinguishing degree acc. to UL94 | V2    |
| Nominal Voltage                        | 1000V |
| Nominal Current                        | 232A  |

## Connection data

|                               |                    |
|-------------------------------|--------------------|
| Rated cross-section solid max | 95 mm <sup>2</sup> |
| Conducting bar                | 25x4 mm            |
| Bolt thread                   | M8 ch13            |

## APPROVALS

EN60947-7-1 95mm<sup>2</sup> – 1000V – 232A

Note : THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES  
AND OTHER COUNTRY REGULATIONS AS PER GS-47-0004

## ACCESSORIES

| Item           | Description                                                 |
|----------------|-------------------------------------------------------------|
| <b>Marking</b> |                                                             |
| 10134314-001LF | Blank large marking tags for SCREW Terminal Blocks PT       |
| 10134315-001LF | Blank large marking tags for cover SCREW Terminal Blocks PT |
| 10134316-001LF | Marking tags adapter for SCREW Terminal Blocks PT           |
| 10134317-001LF | Marking tags adapter for cover SCREW Terminal Blocks PT     |

## DIN RAIL system - Mounting and Installation material

|                |                                                 |
|----------------|-------------------------------------------------|
| 10134392-001LF | Steel Omega Rail TH35x7,5mm -2mt length         |
| 10134393-001LF | Slotted Steel Omega Rail TH35x7,5mm -2mt length |
| 10134394-001LF | Steel Omega Rail TH35x15mm -2mt length          |
| 10134395-001LF | Slotted Steel Omega Rail TH35x15mm -2mt length  |
| 10134387-001LF | Angled support bracket                          |
| 10134389-001LF | End Bracket for TH35 Omega rail -Width 9mm      |
| 10134390-001LF | End Bracket for TH35 Omega rail -Width 6mm      |

## Additional items

|                |                                                |
|----------------|------------------------------------------------|
| 10134322-001LF | End Plate for SCREW Terminal Blocks PT         |
| 10134320-001LF | Cover for SCREW Terminal Blocks PT             |
| 10134321-001LF | Jumper bar for SCREW Terminal Blocks PT70-PT95 |

|               |                    |              |                                   |                                                |              |
|---------------|--------------------|--------------|-----------------------------------|------------------------------------------------|--------------|
| spec ref      | dir Aymeric Soudy  | 23-06-2015   | projection                        | size A3                                        | scale 1:1    |
| tolerance std | eng Aymeric Soudy  | 23-06-2015   |                                   | ecn no                                         |              |
| ISO 406       | chr                |              |                                   | rel level                                      |              |
| ISO 1101      | appr Aymeric Soudy | 23-06-2015   | product family DIN Terminal Block |                                                |              |
| surface ✓     | linear             | 0.X ± 0.3    |                                   | Higt current line-up SCREW Terminal block PT95 |              |
|               |                    | 0.XX ± 0.1   |                                   |                                                |              |
|               |                    | 0.XXX ± 0.05 |                                   |                                                |              |
| ISO 1302      | angular            | 0° ± 2°      | www.fcicom                        | cat. no.                                       |              |
|               |                    |              | Product customer drawing          |                                                | sheet 1 of 1 |

PDS: Rev :A

STATUS:Released

Printed: Jul 17, 2015

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10134309-001LF](#)