

“Stay Connected” with

HEYCO®

Strain Relief Bushings

a PennEngineering® Company

Heyco® RDD Lockit™ Strain Relief Bushings – Right Angle


Snap onto **Flat Cables** for Faster Assembly into **Double D Mounting Holes** –
Semi-Automatic Equipment Available



UL Type	WILL FIT THESE CABLES			PANEL DIMENSIONS				RDD LOCKIT STRAIN RELIEF for Faster Assembly				Corresponding Mounting Hole Plug																		
	AWG/ Conductors	Approximate Size		Mounting Hole Size		Thickness		PART NO.		DESC.	PART NO.	DESC.																		
		in.	mm.	in.	mm.	in.	mm.	Black	White																					
SPT-1	18/2 18/3	.105 x .222 .116 x .315	2,7 x 5,6 2,9 x 8,0	.625 w/ .550 flats	15,9 w/ 14,0 flats	.032	0,8	1806	1807	RDD 100A-90	2497	DD 625-550																		
						.040	1,1																							
						.048	1,2																							
						.063	1,6																							
						.099	2,5																							
SPT-2, HPN	18/2 18/3 16/3	.116 x .315 .160 x .300	2,9 x 8,0 4,1 x 7,6	.625 w/ .550 flats	15,9 w/ 14,0 flats	.032	0,8	1808	1809	RDD 100-90	2497	DD 625-550																		
						.040	1,1																							
						.048	1,2																							
						.063	1,6																							
						.099	2,5																							
HPN	18/3 16/3	.15 x .34 .16 x .37	3,8 x 8,6 4,1 x 9,4	.875 w/ .770 flats	22,2 w/ 19,6 flats	.032 .063 .099 .126 .157	0,8 1,6 2,5 3,2 4,0	1810	1811	RDD 200-90	2509	DD 875-770																		
SPT-2	18/3 16/3	.15 x .40 .16 x .41	3,8 x 10,2 4,1 x 10,4																											
SPT-3	18/2 18/3 16/2 16/3 14/2	.19 x .35 .19 x .39 .20 x .37 .20 x .43 .24 x .42	4,8 x 8,9 4,8 x 9,9 5,1 x 9,4 5,1 x 10,9 6,1 x 10,7																											

Standard color black. Consult Heyco for white and other colors.

- **Right Angle design eases the cable into the bend**, prevents kinking and assures longest cable and product life.
- Assembly friendly! Independent of insertion into the panel, RDD Lockit™ Strain Reliefs self-lock onto the cable. Preassembly RDD Lockits off line for final assembly at a later time or remote location, for lower installed cost!
- Install easily with fingertip pressure into a standard round or Double D hole. No tools required, even for hand assembly.
- Protect the lifeline of your electric/electronic products by absorbing the forces of push and pull that may be exerted on the flexible power cord. Double D design eliminates the possibility of part rotation under forces of twist.
- Multiple panel locking steps secure Lockit Strain Reliefs into a wide range of panel thicknesses for a **flush, finished fit**.
- Heyco's automated Pre-Assembly Equipment speeds assembly of the RDD onto the cable and thus lowers costs while greatly reducing risk of carpal tunnel syndrome. See pages 4-15 & 4-16.
- Consult Heyco for other wire types and sizes.
- See page 4-38 for corresponding **Mounting Hole Plugs** which can be used to fill blank/unused Mounting Holes and thus allow for a single panel design for multiple applications.
- For Double D Mounting Hole Punches, see page 4-30.



Material	Nylon 6/6
Certifications	Recognized under the Component Program of Underwriters' Laboratories File E15331
Flammability Rating	94V-2
Temperature Range	-04°F (-18°C) to 221°F (105°C).

Quick Specs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[1806](#) [1807](#) [1808](#) [1809](#) [1810](#) [1811](#)