



Heyco® RDD Lockit™ Strain Relief Bushings – Straight-Thru


Snap onto **Flat Cables** for Faster Assembly into **Double D Mounting Holes** – *Semi-Automatic Equipment Available*

- **Assembly friendly!** Independent of insertion into the panel, RDD Lockit™ Strain Reliefs **self-lock** onto the cable. Preassemble RDD Lockits off line for final assembly at a later time or remote location, for lower installed cost!
- Install easily with fingertip pressure into a standard round or Double D hole. No tools required, even for hand assembly.
- Protect the lifeline of your electric/electronic products by absorbing the forces of push and pull that may be exerted on the flexible power cord. Double D design eliminates the possibility of part rotation under forces of twist.
- Multiple panel locking steps secure Lockit Strain Reliefs into a wide range of panel thicknesses for a **flush, finished fit**.
- Heyco's automated Pre-Assembly Equipment speeds assembly of the RDD onto the cable and thus lowers costs while greatly reducing risk of carpal tunnel syndrome. See pages 4-15 & 4-16.
- Consult Heyco for other wire types and sizes.
- See page 4-38 for corresponding **Mounting Hole Plugs** which can be used to fill blank/unused Mounting Holes and thus allow for a single panel design for multiple applications.
- **For Quick Specs see page 4-12.**
- For Double D Mounting Hole Punches, see page 4-30.

WILL FIT THESE CABLES				PANEL DIMENSIONS				RDD LOCKIT STRAIN RELIEF for Faster Assembly			Corresponding Mounting Hole Plug											
UL Type	AWG/ Conductors	Approximate Size		Mounting Hole Size		Thickness		PART NO.		DESC.	PART NO.	DESC.										
		in.	mm.	in.	mm.	in.	mm.	Black	White													
SPT-1	18/2 18/3	.105 x .222 .116 x .315	2,7 x 5,6 2,9 x 8,0	.625 w/ .550 flats	15,9 w/ 14,0 flats	.032	0,8	1872	1873	RDD 100A	2497	DD 625-550										
						.040	1,0															
						.048	1,2															
						.063	1,6															
						.099	2,5															
SPT-2, HPN	18/2 18/3 16/3	.116 x .315 .160 x .300	2,9 x 8,0 4,1 x 7,6	.625 w/ .550 flats	15,9 w/ 14,0 flats	.032	0,8	1874	1875	RDD 100	2497	DD 625-550										
						.040	1,0															
						.048	1,2															
						.063	1,6															
						.099	2,5															
HPN	18/3 16/3	.15 x .34 .16 x .37	3,8 x 8,6 4,1 x 9,4	.875 w/ .770 flats	22,2 w/ 19,6 flats	.032 .063 .099 .126 .157	0,8 1,6 2,5 3,2 4,0	1878	1879	RDD 200	2509	DD 875-770										
SPT-2	18/3 16/3	.15 x .40 .16 x .41	3,8 x 10,2 4,1 x 10,4																			
	SPT-3	18/2 18/3 16/2 16/3 14/2	.19 x .35 .19 x .39 .20 x .37 .20 x .43 .24 x .42										4,8 x 8,9 4,8 x 9,9 5,1 x 9,4 5,1 x 10,9 6,1 x 10,7									
Same as RDD 200 above except →													.078 .140	2,0 3,4	1876	1877	RDD 200-2*	2509	DD 875-770			
Same as RDD 200 above except →													1.109 w/ 1.006 flats	28,2 w/ 25,4 flats	.063 .099 .126 .157 .187	1,6 2,5 3,2 4,0 4,8	1798	1799	RDD 510	2717	DD 1109-1000	

Standard color black. Consult Heyco for white and other colors.

* Designed for cast or other mounting holes with rounded edges.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[1872](#) [1874](#) [1878](#) [1798](#) [1799](#) [1874AA](#)