



ITEM #	PART #	QTY	DESCRIPTION	MATERIAL
1	AP-176-1	1	SHELL ASS'Y	GLASS FILLED NYLON & 303 SS
2	AP-146-6	1	INSERT ASS'Y	DIALLYPHTHALATE, TYPE SDGF & GOLD PLATED BRASS
3	AP-105-5	1	STRAIN RELIEF	NYLON
4	AP-116-3	1	WASHER	RUBBER
5	AP-136-8	1	NUT ADAPTER	ALUMINUM, BLACK CHROME
6	AP-136-6	1	CLAMP SHIELD, OUTER	NICKEL PLATED BRASS
7	AP-136-5	1	CLAMP SHIELD INNER	NICKEL PLATED BRASS
8	SEE TABLE #1	1	BUSHING	RUBBER
9	AP-116-2	1	WASHER	STAINLESS STEEL
10	AP-116-4	1	SPRING	302 STAINLESS STEEL
11	AP-116-6	1	STUD	ANODIZED ALUMINUM ALLOY

TABLE #1		
PART #	CABLE DIA	BUSHING
AP-176-01	Ø .165 ± .010	AP-116-17
AP-176-02	Ø .228 ± .010	AP-116-18
AP-176	Ø .250 ± .010	AP-116-8
AP-176-04	Ø .2905 ± .010	AP-116-19

CAP-176

NOTES:
1) UNLESS OTHERWISE SPECIFIED, CONNECTOR MEETS ALL
GENERAL REQUIREMENTS & SPECIFICATIONS OF MIL-C-55116

ORANGE
ALIGNMENT
MARK



SECTION Z-Z

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

					WITHOUT THE WRITTEN CONSENT OF NEXUS.					
					DWN.BY MNF	DATE 5/22/95	MATERIAL			
D	ADD P/N'S TO P/L	101	2/25 2011	HR	CHECKED BY L SMITH	DATE 5/22/95	FINISH			
C	3) IN MAT'L'S REMOVE WITH SS PINS 2) NOTE 2 WAS AP-176-1 1) REMOVE PRESSED IN PIN	045	2/12 2010	GPH	APPR.BY L SMITH	DATE 5/22/95	WEIGHT	SCALE = 1.00 :1	NEXUS STAMFORD,CONN	
B	3)"XUS" WAS "-176" 2) AP-175-1 WAS AP-176-XA 1) AP-176-1 WAS AP-176-2	0394	2/24 2000	EWT	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES & OR [mm] TOLERANCES: DECIMAL: ±.XX[X.X] ±.01[0.3] ±.XXX[X.XX] ±.003[0.08] FRACTION: ±XXX ± 1/64 ANGLES: ±X ° ±5 °		TITLE AUDIO PLUG			
A	REVISED & REDRAWN ON CAD	0259	2/24 1997	LS						
LET.	REVISION	CN #	DATE	CHK	DO NOT SCALE DWG.		SHEET 1 OF 1			SIZE C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AP-176](#) [AP-176/02](#) [AP-176/04](#) [AP-176/03](#) [AP-176/01](#) [AP-176RA/5](#) [AP-176SPE](#) [AP-176RA/3](#)