





COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE

RECOMMENDED PC BOARD HOLE PATTERN



PART No.	CODE No.	A	B
A1- 4PA-2.54DSA(71)	CL619-0036-1-71	4.78	2.54
A1- 6PA-2.54DSA(71)	CL619-0021-4-71	7.32	5.08
A1- 8PA-2.54DSA(71)	CL619-0037-4-71	9.86	7.62
A1-10PA-2.54DSA(71)	CL619-0022-7-71	12.40	10.16
A1-12PA-2.54DSA(71)	CL619-0023-0-71	14.94	12.70
A1-14PA-2.54DSA(71)	CL619-0024-2-71	17.48	15.24
A1-16PA-2.54DSA(71)	CL619-0025-5-71	20.02	17.78
A1-18PA-2.54DSA(71)	CL619-0026-8-71	22.56	20.32
A1-20PA-2.54DSA(71)	CL619-0027-0-71	25.10	22.86
A1-24PA-2.54DSA(71)	CL619-0028-3-71	30.18	27.94
A1-26PA-2.54DSA(71)	CL619-0029-6-71	32.72	30.48
A1-30PA-2.54DSA(71)	CL619-0030-5-71	37.80	35.56
A1-34PA-2.54DSA(71)	CL619-0031-8-71	42.88	40.64
A1-40PA-2.54DSA(71)	CL619-0032-0-71	50.50	48.26
A1-50PA-2.54DSA(71)	CL619-0033-3-71	63.20	60.96
A1-60PA-2.54DSA(71)	CL619-0034-6-71	75.90	73.66
A1-64PA-2.54DSA(71)	CL619-0035-9-71	80.98	78.74

NOTES 1. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
2. NUMBER OF CONTACTS.

1	PBT	BLACK	UL94V-0	2	BRASS	CONTACT AREA : GOLD 0.2μm min DIP AREA : TIN-PLATING 2μm min UNDER PLATING : NICKEL 2.5μm min			
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS				
CODE NO. (OLD) CL		DRAWN K. NAKAMURA		DESIGNED K. NAKAMURA	CHECKED H. Ogawa	APPROVED H. Ogawa	RELEASED		
SCALE FREE		06.01.23		06.01.23	06.01.23	06.01.23			
UNITS mm		DRAWING NO. EDC3-152791-21		PART NO. A1-**-PA-2.54DSA(71)		CODE NO. CL619			
HIROSE ELECTRIC CO., LTD		6		7		8			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[A1-10PA-2.54DSA\(71\)](#)