




# “Stay Connected with Heyco” Hardware




## HEYClip™ Nylon Wire Clips

### Adhesive-Backed

MAXIMUM BUNDLE DIAMETER		RATED STATIC LOAD	PART NO. Adhesive			DESCRIPTION	FOOTPRINT		OVERALL HEIGHT		CLAMP WIDTH	
in.	mm.		Standard Gray	Black	Super Gray		A x B		in.	mm.	in.	mm.
.187	4,7	1/2	3857	3917	-	WCA 187-500	.74 x .62	18,8 x 15,7	.34	8,6	.39	9,9
.250	6,4	3/4	3858	3918	3858A	WCA 250-750	1.00 x .87	25,4 x 22,1	.42	10,7	.63	16,0
.375	9,5	1	3859	3919	3859A	WCA 375-1000	1.00 x 1.00	25,4 x 25,4	.50	12,7	.63	16,0
.500	12,7	1-1/4	3860	3920	3860A	WCA 500-1250	1.00 x 1.21	25,4 x 30,7	.68	17,3	.64	16,3
.750	19,1	1-3/4	3861	3921	-	WCA 750-1750	1.15 x 1.45	29,2 x 36,8	.99	25,1	.64	16,3
1.000	25,4	4	3867	3923	-	WCA1000-4000	1.98 x 2.24	50,3 x 56,9	1.37	34,8	1.26	32,0
1.500	38,1	6	3868	3930	-	WCA 1500-6000	2.42 x 2.95	61,5 x 74,9	1.77	45,0	1.31	33,3


Standard color gray or black. Super duty adhesive backing available as shown.

- Releasable and reusable clips for easy wire bundle routing.
- Quick and easy installation—simply peel off backing and press into place.
- Made of Nylon 6/6 with a 94V-2 flammability rating.
- Seven sizes for bundles from .187” (4,7 mm) to 1.500” (38,1 mm) in diameter.
- Apply to a clean, dry surface.
- Three sizes in Super Adhesive Gray.
- Super adhesive temperature range is -40°F (-40°C) to 250°F (121°C).




## HEYClip™ Installation Instructions


### Adhesive-Backed Wire Clips



HEYClip attaches easily to any commercial surface. Backing strips off easily.



Unique closure operates easily, locks securely. When closed, HEYClip will not release until push tab is released.



HEYClip opens easily to permit removal of bundle.

<b>Material</b>	Nylon 6/6
<b>Flammability Rating</b>	94V-2
<b>Temperature Range</b>	-20°F (-29°C) to 150°F (66°C)
<b>Recommended Storage Temperature</b>	From 60°F (16°C) to 80°F (27°C) with approximate relative humidity of 50%
<b>Rated Static Loads</b>	Pertain to parts fastened to a flat, clean, and dry surface

*Quick Specs*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3788](#)