



Heyco® Open/Closed Universal Bushings


Mounting Hole Diameter Range: .500" (12,7 mm) to 2.500" (63,5 mm)

- **Split design allows side entry** and encirclement of preassembled harnesses, power cords, capillary tubes or other assemblies that have segments larger than the bushing's ID.
- Parts can be assembled into holes that already contain cables or tubing.
- Only fingertip pressure required to snap-lock the bushing into its mounting hole.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Flexible shutters adjust to accommodate and support any shape from .125" (3,2 mm) to a maximum inside diameter of 1.970" (43,2 mm).
- Absorb vibration, cushion and insulate cables, tubing, hoses or shafts.
- Available in multiple sizes for use in .500" (12,7 mm) to 2.500" (63,5 mm) diameter holes.

MOUNTING HOLE DIAMETER		PART NO. Black	DESCRIPTION	PART DIMENSIONS					
in.	mm.			Maximum Inside Diameter		A Head Diameter		B Overall Height	
				in.	mm.	in.	mm.	in.	mm.
Multiple Locking Steps for Panel Thickness up to .125" (3,2 mm)									
.500	12,7	2055SP	OCUB 500	.31	7,6	.56	14,2	.39	9,8
.625	15,9	2077SP	OCUB 625	.44	11,1	.69	17,5		
.750	19,1	2089SP	OCUB 750	.50	12,7	.50	20,3		
.875	22,2	2119SP	OCUB 875	.56	14,3	.92	23,4		
1.000	25,4	2137SP	OCUB 1000	.75	19,1	1.05	26,7	.41	10,3
1.093	27,8	2157SP	OCUB 1093	.81	20,6	1.16	29,5		
1.250	31,8	2196SP	OCUB 1250	.94	23,8	1.44	36,6		
1.375	34,9	2184SP	OCUB 1375	1.00	25,4	1.44	36,6		
1.500	38,1	2213SP	OCUB 1500	1.06	26,9	1.56	39,6	.42	10,7
2.000	50,8	2422SP	OCUB 2000	1.64	41,7	2.12	53,9		

Multiple Locking Steps for Panel Thickness up to .250" (6,4 mm)									
2.500	63,5	2440SP	OCUB 2.5	1.97	43,2	2.60	66,0	.72	18,3

Standard color black. Consult Heyco for white and other colors.



Quick Specs

Material	Nylon 6/6
Certifications	Recognized under the Component Program of Underwriters' Laboratories, File E15331 Certified by the Canadian Standards Association, File 8919
Flammability Rating	94V-2
Temperature Range	-4°F (-18°C) to 221°F (105°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[2184SP](#) [2077SP](#) [2089SP](#) [2157SP](#) [2196SP](#) [2213SP](#) [2137SP](#) [2422SP](#) [2440SP](#) [2055SP](#) [2119SP](#)