





Heyco® Nylon PCB Supports

Locking Reverse PCB Supports

PANEL DIMENSIONS				PCB DIMENSIONS				PART NO.	DESCRIPTION	PART DIMENSIONS																					
Maximum Thickness		Mounting Hole Diameter		Maximum Thickness		Mounting Hole Diameter				A Spacing		B Head Length		C Foot Length																	
in. mm.		in. mm.		in. mm.		in. mm.				in. mm.		in. mm.		in. mm.																	
SS LR Series																															
.06		1,6		.187		4,8		.06		1,6		.125		3,2		3699		SS LR 5/16		.31		7,9									
																3700		SS LR 3/8		.38		9,5		.06		1,5		.19		4,8	
																3701		SS LR 7/16		.44		11,1									

Standard color natural.



Stacking Retainer Supports

PANEL DIMENSIONS				PCB DIMENSIONS				PART NO.	DESCRIPTION	PART DIMENSIONS					
Maximum Thickness		Mounting Hole Diameter		Screw Size	Maximum Thickness		A Spacing			B Outside Diameter		C Inside Diameter			
in.	mm.	in.	mm.		in.	mm.	in.			mm.	in.	mm.	in.	mm.	
SS RS Series															
.06	1,6	.187	4,8	#4	.06	1,6	3681	HSSRS4-02	.13	3,2	.26	6,6	.13	3,2	
							3683	HSSRS4-03	.19	4,8					
							3684	HSSRS4-04	.25	6,4					
							3685	HSSRS4-06	.38	9,5					
							3687	HSSRS4-08	.50	12,7					
							3688	HSSRS4-10	.63	15,9					
	.234	6,0	#6	.06	1,6	3689	HSSRS6-04	.25	6,4	.31	7,9	.15	3,9		
						3690	HSSRS6-06	.38	9,5						
						3691	HSSRS6-08	.50	12,7						
						3692	HSSRS6-10	.63	15,9						
			#8	.06	1,6	3693	HSSRS8-04	.25	6,4	.31	7,9	.17	4,3		
						3694	HSSRS8-06	.38	9,5						
						3695	HSSRS8-08	.50	12,7						
						3696	HSSRS8-10	.63	15,9						

Standard color natural.

- Durable, lightweight, and high strength design.
- Locking Reverse PCB Supports are **ideal for minimal clearance locations** and suitable for chassis-to-board requirements.



- Stacking Retainer Supports are suitable for **board to board and chassis to board** requirements.
- Easily installed without tools.

Material: Nylon 6/6
 Flammability Rating: 94-V0
 Temperature Range: 32°F (0°C) to 185°F (85°C)

Quick Specs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Heyco:

[3684](#) [3691](#) [3685](#) [3688](#) [3683](#) [3696](#) [3689](#) [3681](#) [3695](#) [3693](#) [3687](#) [3692](#) [3690](#) [3694](#)