





Heyco® Original Strain Relief Bushings

Straight-Thru for Round Cables


.625" (15,9 mm) to .750" (19,0 mm) Mounting Holes




WILL FIT THESE CABLES				PANEL DIMENSIONS						PART NO.	DESCRIPTION	PART DIM.		Mounting Hole Plug		
UL Type	AWG/ Conductors	Approximate Size		A Mounting Hole Dia.		B To Prevent Rotation		Finished Fit Panel Thickness*		Black		C BODY LENGTH		PART NO.		
		in.	mm.	in.	mm.	in.	mm.	in.	mm.			in.	mm.			
SJ, SJT & SJO	18/2	.300	7,6	.625	15,9	.550	14,0	.062	1,6	1217	SR 6N-4	.578	14,7	2497		
Same as SR 6N-4 above except 									.125	3,2	1210	SR 6P-4	.578		14,7	
SJT	18/3	.300-.330	7,6-8,4	.625	15,9	.550	14,0	.062	1,6	1197	SR 6N2-4	.578	14,7			
SJ, SJT & SJO	16/2	.325	8,3	.625	15,9	.550	14,0	.062	1,6	1200	SR 6N3-4	.578	14,7			
	18/3	.330	8,4													
	14/2	.350	8,9													
	16/3	.355	9,0													
	18/4	.360	9,1	Same as SR 6N3-4 above except 							.125	3,2	1207	SR 6P3-4	.578	14,7
S & ST	18/2	.380	9,7	.625	15,9	.550	14,0	.062	1,6	1202	SR 6N5-4	.578	14,7			
	18/3	.405	10,3													
Same as SR 6N5-4 above except 									.125	3,2	1204	SR 6P5-4	.578	14,7		
SJ, SJT & SJO	18/2	.300	7,6	.625	15,9	.550	14,0	.156	4,0	1214	SR 6L-1	.678	17,2	consult Heyco		
	16/2	.325	8,3	.656	16,7											
	18/3	.330	8,4	.656	16,7											
	16/3	.355	9,0	.687	17,4											
HPD	16/3	.355	9,0	.687	17,4											
SJT	18/4	.360	9,1	.750	19,0	.660	16,8	.062	1,6	1244	SR 7N-2	.750	19,1	2503		
	14/3	.370	9,4													
S & ST	18/2	.390	9,9	.750	19,0	.660	16,8	.062	1,6	1244	SR 7N-2	.750	19,1			
	18/3	.405	10,3													
	16/2	.405	10,3													
	16/3	.430	10,9													
									.750	19,0	.781	19,8				
Same as SR 7N-2 above except 									.125	3,2	1237	SR 7P-2	.750	19,1		

Standard color black. Consult Heyco for white and other colors.


*Maximum Panel Thickness. Part has additional clearance. Consult Heyco for your Custom Finished Fit Panel Thickness.




FOR SR-7KR-2 ONLY



STANDARD MOUNTING HOLES



ELONGATED MOUNTING HOLE



- **Protects the lifeline of your electric/electronic products** by absorbing the forces of pull, push, and twist that may be exerted on the flexible power cord.
- Securely anchors, insulates, and protects cables at panel entry points.
- Sizes SR 6-Series to SR 7-Series for mounting hole diameters from .625" (15,9 mm) to .781" (19,8 mm).
- Sizes for thin .062" (1,6 mm) panel available: SR 7N-2 See chart for details.
- See page 4-38 for corresponding **Mounting Hole Plugs** which can be used to fill blank/unused Mounting Holes and thus allow for a single panel design for multiple applications.
- Consult Heyco for other wire types and sizes.
- See pages 4-27 & 4-28 for SR assembly tools.
- **See page 4-19 for Quick Specs.**
- For Double D Mounting Hole Punches, see page 4-30.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[1200](#)