


## Heyco® RDD Lockit™ Strain Relief Bushings – Pigtail™

Snap onto **Flat or Round Cables** for Faster Assembly into **Double D Mounting Holes** – *Semi-Automatic Equipment Available*




WILL FIT THESE CABLES				PANEL DIMENSIONS				RDD LOCKIT STRAIN RELIEF for Faster Assembly			Corresponding Mounting Hole Plug	
UL Type	AWG/ Conductors	Approximate Size		Mounting Hole Size		Thickness		PART NO.		DESC.	PART NO.	DESC.
		in.	mm.	in.	mm.	in.	mm.	Black	White			
For Flat Cables												
SPT-1	18/2 18/3	.105 x .222 .116 x .315	2,7 x 5,6 2,9 x 8,0	.625 w/ .550 flats	15,9 w/ 14,0 flats	.032	0,8	1769	1770	RDD 100A-7	2497	DD 625-550
						.040	1,1					
						.048	1,2					
						.063	1,6					
						.099	2,5					
SPT-2, HPN	18/2 18/3 16/3	.116 x .315 .160 x .300	2,9 x 8,0 4,1 x 7,6	.625 w/ .550 flats	15,9 w/ 14,0 flats	.032	0,8	1771	1772	RDD 100-7	2497	DD 625-550
						.040	1,1					
						.048	1,2					
						.063	1,6					
						.099	2,5					
For Round Cables												
See table on page 4-10	various	.220-.290	5,6 x 7,4	.625 w/ .550 flats	15,9 w/ 14,0 flats	.032	0,8	1773	1774	RDD 101-7	2497	DD 625-550
						.040	1,1					
						.048	1,2					
						.063	1,6					
						.099	2,5					

Standard color black. Consult Heyco for white and other colors.



RDD 100A-7, RDD 100-7, RDD 101-7

Locking Tab varies with Cable Type



- **Integral nylon spring eases the cable into a lazy bend;** prevents kinking and assures longest cable and product life.
- Designed to pass CSA's 50,000 cycle vacuum cleaner test ( C22.2 No. 67) and UL's 859 specification for Household Electric Personal Grooming Appliances Cord Flexing Test.
- Assembly friendly! Independent of insertion into the panel, RDD Lockit™ Strain Reliefs self-lock onto the cable. Preassembly RDD Lockits off line for final assembly at a later time or remote location, for lower installed cost!
- Install easily with fingertip pressure into a standard round or Double D hole. No tools required, even for hand assembly.
- Protect the lifeline of your electric/electronic products by absorbing the forces of push and pull that may be exerted on the flexible power cord. Double D design eliminates the possibility of part rotation under forces of twist.
- Multiple panel locking steps secure Lockit Strain Reliefs into a wide range of panel thicknesses for a **flush, finished fit**.
- Heyco's automated Pre-Assembly Equipment speeds assembly of the RDD onto the cable and thus lowers costs while greatly reducing risk of carpal tunnel syndrome. See pages 4-15 & 4-16.
- See page 4-38 for corresponding **Mounting Hole Plugs** which can be used to fill blank/unused Mounting Holes and thus allow for a single panel design for multiple applications.
- For Double D Mounting Hole Punches, see page 4-30.

Material  
Certifications

Nylon 6/6

Recognized under the Component Program of Underwriters' Laboratories File E15331

Certified by the Canadian Standards Association File 8919

Flammability Rating  
Temperature Range

94V-2

-04°F (-18°C) to 221°F (105°C)

*Quick Specs*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[1772](#)