




PART No.	CODE No.		A	B
A1- 4PA-2.54DSA(71)	CL619-0036-1-71	4	4.78	2.54
A1- 6PA-2.54DSA(71)	CL619-0021-4-71	6	7.32	5.08
A1- 8PA-2.54DSA(71)	CL619-0037-4-71	8	9.86	7.62
A1-10PA-2.54DSA(71)	CL619-0022-7-71	10	12.40	10.16
A1-12PA-2.54DSA(71)	CL619-0023-0-71	12	14.94	12.70
A1-14PA-2.54DSA(71)	CL619-0024-2-71	14	17.48	15.24
A1-16PA-2.54DSA(71)	CL619-0025-5-71	16	20.02	17.78
A1-18PA-2.54DSA(71)	CL619-0026-8-71	18	22.56	20.32
A1-20PA-2.54DSA(71)	CL619-0027-0-71	20	25.10	22.86
A1-24PA-2.54DSA(71)	CL619-0028-3-71	24	30.18	27.94
A1-26PA-2.54DSA(71)	CL619-0029-6-71	26	32.72	30.48
A1-30PA-2.54DSA(71)	CL619-0030-5-71	30	37.80	35.56
A1-34PA-2.54DSA(71)	CL619-0031-8-71	34	42.88	40.64
A1-40PA-2.54DSA(71)	CL619-0032-0-71	40	50.50	48.26
A1-50PA-2.54DSA(71)	CL619-0033-3-71	50	63.20	60.96
A1-60PA-2.54DSA(71)	CL619-0034-6-71	60	75.90	73.66
A1-64PA-2.54DSA(71)	CL619-0035-9-71	64	80.98	78.74

NOTES 1. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
2. NUMBER OF CONTACTS.

					2	BRASS	CONTACT AREA : GOLD 0.2μm min.		
							DIP AREA : TIN-PLATING 2μm min.		
							UNDER PLATING : NICKEL 2.5μm min.		
1	PBT	BLACK 							
NO.	MATERIAL	FINISH . REMARKS			NO.	MATERIAL	FINISH . REMARKS		
UNITS mm		SCALE FREE		COUNT 2	DESCRIPTION OF REVISIONS DIS-F-00015681		DESIGNED YU. NAKADA	CHECKED HT. YAMAGUCHI	DATE 20221021
 HIROSE ELECTRIC CO., LTD.		APPROVED : HS. OKAWA		20060123	DRAWING NO.		EDC-152791-71-21		
		CHECKED : HS. OZAWA		20060123	PART NO.		A1-*PA-2. 54DSA(71)		
		DESIGNED : KY. NAKAMURA		20060123	CODE NO.		CL619		
		DRAWN : KY. NAKAMURA		20060123			 		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[A1-10PA-2.54DSA\(71\)](#)