






Oct.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

△(Part No.4 shape change)




Notes. 1. Applicable cable condition is shown below.
In case of using a not applicable cable, please contact our sales representative.
Refer to the technical specification (ETAD-E3164-00) for wiring and assembly procedure.

Applicable Cable	
Items	Applicable Condition
Conductor size	AWG # 28-22
Insulation O.D.	φ 1.55 mm MAX.
Braid Shield	Tin plating
Sheath O.D.	φ 6.3 -7.2 mm




2. This product (Type B) is used for non Ethernet applications
like signaling, serial or other industrial bus communication systems.
Please use Type A for 10/100Mbit/s and 1/10 Gbit/s Ethernet communication.



3. This product except plug unit is packed separately by the types of parts.
Shield Shell is packed in pre-bended state.(See next page.)

3	Stainless Steel				
2	PA	Black, UL94V-0	7	PC	Dark gray, UL94V-0
1	Copper Alloy	Contact area : Palladium-Nickel 0.75 μm min + Gold 0.05 μm min Wiring area : Gold 0.03 μm min Under plating : Nickel 2 μm min	6	Stainless Steel	Nickel 0.2 μm min
			5	Stainless Steel	Nickel 1 μm min
			4	PA	Black, UL94V-0
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-E-00003265	DESIGNED KI. KAGOTANI
HIROSE ELECTRIC CO., LTD.		APPROVED : RI. TAKAYASU	20170411	DRAWING NO. EDC-129507-01-00	
		CHECKED : KI. NAGANUMA	20170411	PART NO. IX40G-B-10S-CV<7.0><01>	
		DESIGNED : TS. SAKAIZAWA	20170411	CODE NO. CL251-0032-0-01	
		DRAWN : TS. SAKAIZAWA	20170411	1/2	

Oct.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[IX40G-B-10S-CV\(7.0\)\(01\)](#)