

DE Series

DE

2

L

-

A

A

A

A

コード Code	定格 Rating	VDE/SEMKO
1	3 A, 30 VDC 3 A, 125-250 VAC	3 A, 30 VDC
2	5 A, 30 VDC 1 A, 42 VDC	5 A, 30 VDC 1 A, 42 VDC
3	0.1 A, 30 VDC 0.1 A, 125-250 VAC	0.1 A, 30 VDC

コード Code	UL認定寿命 UL Approval (Life Test Cycle)
C	6,000 回 6,000 Cycles
L	100,000 回 (DC定格) 100,000 Cycles (DC)

コード Code	端子形状 Terminal Configuration
A	はんだ端子 Short Solder 2.8×0.8
B	#110Q.C. (Short) 2.8×0.5Q.C. $\phi=8$
C	PCB PCB1×0.8
D	PCBライト PCB Right 1×0.8
E	PCBレフト PCB Left 1×0.8
F	#110Q.C. (Long) 2.8×0.5Q.C. $\phi=9.6$
H	PCB KINK PCB1×0.8 Self-standing

コード Code	回路構成 Circuitry
A	単極双投 S.P.D.T. NC/NO
B	単極単投 (NO) S.P.S.T. NO only
C	単極単投 (NC) S.P.S.T. NC only

コード Code	アクチュエータ長 Auxiliary Actuator-length			
	B	C	D	G
ボタンタイプ Button	AA			
ストレートレバー Straight	L	4.8	7	42
ローラー Roller	R	2.5	4.7	39.7
シュミレート Simulated roller	S	2.5	4.7	39.7



General Part number

DE1L-AAAA	DE1L-DAAA	DE2L-AAAA	DE2L-DAAA	DE3L-AAAA
DE1L-AALB	DE1L-DALB	DE2L-AALB	DE2L-DALB	DE3L-AALB
DE1L-AALC	DE1L-DASC	DE2L-AALC	DE2L-DALC	DE3L-AALD
DE1L-AALD	DE1L-EAAA	DE2L-AALD	DE2L-DARC	DE3L-AARB
DE1L-AARB	DE1L-EALB	DE2L-AARC	DE2L-DBAA	DE3L-AARD
DE1L-AASC	DE1L-EASC	DE2L-AASB	DE2L-DBLG	DE3L-AASB
DE1L-BAAA	DE1L-FAAA	DE2L-AASC	DE2L-EAAA	DE3L-AASC
DE1L-BALB	DE1L-FALC	DE2L-ABLC	DE2L-EALB	DE3L-BAAA
DE1L-BALC		DE2L-BAAA	DE2L-EALD	DE3L-BALB
DE1L-BALD		DE2L-BALB	DE2L-EARC	DE3L-BALC
DE1L-BARB		DE2L-BALD	DE2L-EBLB	DE3L-BARB
DE1L-BASC		DE2L-BALG	DE2L-FAAA	DE3L-BASC
DE1L-CAAA		DE2L-BARC	DE2L-FALB	DE3L-CAAA
DE1L-CALB		DE2L-CAAA	DE2L-FALC	DE3L-CALB
DE1L-CASB		DE2L-CALB	DE2L-FASB	DE3L-CASB
DE1L-CASC		DE2L-CALC	DE2L-HBLB	DE3L-DAAA
DE1L-CASD		DE2L-CARC	DE2L-HBLG	DE3L-EAAA
				DE3L-FAAA
				DE3L-FALB
				DE3L-FALC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[DE2L-AAAAY](#) [DE2L-AALBY](#) [DE2L-ABLCY](#) [DE2L-BAAAY](#) [DE2L-BALBY](#) [DE3L-BBLCY](#) [DE2L-BALGY](#) [DE2L-](#)
[EALBY](#) [DE2L-FAAAY](#) [DE2L-FALBY](#) [DE3L-AALBY](#) [DE3L-ABLCY](#)