








May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV, RoHS COMPLIANT



RECOMMENDED PCB PATTERN



- NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.)
USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C 90~120s
2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
3. CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm.
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.
6. : Pattern prohibited area





2		BRASS	SURFACE PLATING : TIN PLATING 1μm min UNDER PLATING : NICKEL 1μm min	6	POLYESTER	
1		PA	BLACK UL94V-0	5	POLYSTYRENE	
NO.		MATERIAL	FINISH . REMARKS	4	POLYIMIDE	PICK & PALCE TAPE
				3	BRASS	SURFACE PLATING : TIN PLATING 1μm min UNDER PLATING : NICKEL 1μm min
				NO.	MATERIAL	FINISH . REMARKS
UNITS		mm	SCALE 2 : 1	COUNT DESCRIPTION OF REVISIONS		
				DESIGNED		
				CHECKED		
				DATE		
				APPROVED : HK. UMEHARA 20190730		
				CHECKED : OM. MIYAMOTO 20190729		
				DESIGNED : TY. ISHIGURO 20190729		
				DRAWN : DS. HIROWATARI 20190712		
				DRAWING NO. EDC-376619-00-00		
				PART NO. ZE05H-12DP-2V		
				CODE NO. CL752-2313-0-00		
				1/2		

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


PACKING STYLE

REEL DIMENSION (FREE)

PACKING STYLE DRAWING



CARDBOARD DIMENSION (FREE)



HRS	DRAWING NO.	EDC-376619-00-00
	PART NO.	ZE05H-12DP-2V
	CODE NO.	CL752-2313-0-00
		2 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[ZE05H-12DP-2V](#)