

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A



A DIVISION OF HONEYWELL INC.

FED. MFG. CODE 91929

SWITCH - BASIC

V7-IB17D8-048-S

CW-84719




NOTES

1 - CAUTION: OVERTRAVEL FORCE ON LEVER MUST NOT RESULT IN AN OVERTRAVEL FORCE ON PLUNGER EXCEEDING 5 POUNDS

2 CHARACTERISTICS ARE APPROXIMATE WITHOUT RUBBER SEAL BOOT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE ----- 50 GRAM (APPROX)	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
	L 156	ONE PLACE (.0) ± .030	
	11A 1/3 HP 125, 250, 277 VAC	TWO PLACE (.00) ± .015	
	1/2A 125 VDC, 1/4A 250 VDC	THREE PLACE (.000) ± .005	
	4A 125 VAC "L"	ANGLES ±	
	ALC		
		WEIGHT	

V7-IB17D8-048-S

DRAWING NUMBER

ISSUE

REVISIONS

A 17032

S D

10 JAN 89

B CO

65617-A

D CS

11 MAY 89

C CO

76109

JWB

8 NOV 93

D CO

77796

D CS

23 MAR 94

FO-52848-B

DRAWN

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

FO-52848-B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-1B17D8-048-S](#)