

**MICRO SWITCH**A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY  
PASADENA, CALIFORNIA

FED. MFR. CODE 91929

**ACTUATOR - SWITCH**

CATALOG LISTING

**JX - 44****JX - 44**

REPLACES

RELEASE NO. SR-10742

**M**DRAWING  
NUMBER**28****28**

ISSUE

**28**

## REVISIONS

A CO15829

M B F

17 APRIL 61

B SR-10742

R E R

18 JAN 63

C CO22579

O M W

1 MAY 67

D CO23793

W E B

6 FEB 68

E CO22579

M B S

19 APR 68

F CO30270

S R H

29 FEB 72

G CO62929

D L T

13 MAY 96

CHECK

29 AUG 60

FWF

18 JAN 63

FWF

6 FEB 68

FWF

21 JAN 63

FWF

FWF

FWF

FWF



FWF

FWF

FWF

FWF

FWF



## NOTE -

SLIGHT ROTATION BETWEEN BASIC AND ACTUATOR MAY BE NECESSARY  
TO OBTAIN OPERATING POSITION, BASED ON USING  
NO. 2-56 MACHINE SCREWS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

**CHARACTERISTICS** WITH ISKI-T BASIC  
SWITCH INSTALLED

OPERATING FORCE — — — — 7 OZ MAX

RELEASE FORCE — — — — 2 OZ MIN

DIFFERENTIAL TRAVEL — — — .025 MAX

OVERTRAVEL — — — — .015 MIN

**ELECTRICAL DATA**

CONTACT ARRANGEMENT

BREAK DISTANCE

SCALE 2 TO 1

DO NOT SCALE PRINT

UNLESS OTHERWISE  
SPECIFIED

DIMENSIONS ARE IN INCHES

**TOLERANCES ARE:**ONE PLACE (.0) ± .030  
TWO PLACE (.00) ± .015  
THREE PLACE (.000) ± .005  
ANGLES ±

WEIGHT

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[JX-44](#)