

173-501APC-301

(Home (/index.php?ci_id=3972&la_id=1) : Products (/products) : Sensors : Temperature Sensors : Discrete Thermistors : 173)

Distributor Inventory

Input part number for stock availability



173 Series, surface mounted device 0805, 500 Ohm resistance, ±1.0% tolerance, 25/85 BETA = 3250

Actual product appearance may vary.

Sales & Service

Distributor Inventory

Narrow Your Search

Modify Your Search

Products

Technology

Industries Served

OverviewSpecsDocumentationApplication Notes

Product Specifications	
Availability	Global
Resistance	500 Ohm
Tolerance	±1.0%
Accuracy	25 °C [77 °F]
Beta	3250
Operating Temperature	-60 °C to 125 °C [-76 °F to 257 °F]
Diameter	EIA 0805 SMD
Time Constant in Air	10.0 s
Dissipation Constant	3,5 m/W°C
Series Name	173

Product Search

Product Type: All Product Types

Industry: All Industries

Search Term: Start Here ...

☐ New Products Only

☒ Entire Product Catalog

Search

My Links

eCOM Login (/index.php?ci_id=50629&la_id=1)

Request Access to eCOM (/ecom access request)

Rep/AD Portal Login (/index.php?)

Literature and Media

Data Sheets (/w hite paper and technical data sheets library)

Videos (/videos)

Literature (/literature)

Contacts

Customer Service (/index.php?ci_id=50608&la_id=1)

Technical Support (/index.php?ci_id=50609&la_id=1)

ci_id=50606&la_id=1) Rep/AD Portal Access Request (/index.php?ci_id=50630&la_id=1) Sample Request (/samplerequest) Digital University Login (/index.php?ci_id=50607&la_id=1) Limitless Microsite (/index.php?ci_id=50603&la_id=1) Supplier Microsite (/index.php?ci_id=44887&la_id=1)	Literature Request (/index.php?ci_id=50636&la_id=1) White Papers (/w hitepapers) Application Notes (/application notes) Application Demos (/index.php?ci_id=141383&la_id=1) CAD Renderings (/cad renderings)	Global Sales & Service (/index.php?ci_id=50610&la_id=1) Website Feedback (/index.php?ci_id=142628&la_id=1)
 http://www.youtube.com/user/SensingAndControl/videos	Terms & Conditions (/index.php?ci_id=2588&la_id=1)	Privacy Statement (/index.php?ci_id=2589&la_id=1) Site Map (/sitemap)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[173-501APC-301](#)