

IDENTIFICATION

I L - Z _ * * S _ S 1 2 5 C 3 - *

APPLICABLE WIRE: AWG#28, 30, 32

(CRIMP)

(1 . 25 mm) [. 049]

(S I N G L E)

S : S O C K E T C O N T A C T

NO. OF CONTACTS

SERIES

PART NO.	NO. OF CONTACT	A ± 0.25 [.010]	B ± 0.15 [.006]	D -0.3 ($-.012$)
1L-Z-2S-S125C3-*	2	3.95 [.156]	1.25 [.049]	3.25 [.128]
3	3	5.2 [.205]	2.5 [.098]	4.5 [.177]
4	4	6.45 [.254]	3.75 [.148]	5.75 [.226]
5	5	7.7 [.303]	5 [.197]	7 [.276]
6	6	8.95 [.352]	6.25 [.246]	8.25 [.325]
7	7	10.2 [.402]	7.5 [.295]	9.5 [.374]
8	8	11.45 [.451]	8.75 [.344]	10.75 [.423]
9	9	12.7 [.500]	10 [.394]	12 [.472]
10	10	13.95 [.549]	11.25 [.443]	13.25 [.522]
11	11	15.2 [.598]	12.5 [.492]	14.5 [.571]
12	12	16.45 [.648]	13.75 [.541]	15.75 [.620]
13	13	17.7 [.697]	15 [.590]	17 [.669]
14	14	18.95 [.746]	16.25 [.640]	18.25 [.718]
1L-Z-15S-S125C3-*	15	20.2 [.795]	17.5 [.689]	19.5 [.768]

ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	REMARKS
REFERENCE DOCUMENT		DATE 6 . JUL. '90	SCHEMATIC WT DRAWN E. MURANO	TITLE I L - Z - * * S - S 1 2 5 C 3 - *	 Reference MUSASHINO, AKISHIMA-SHI TOKYO, JAPAN
MATERIAL GLASS FILLED 6-6NY		CHECKED I. IGARASHI	APP'D —	SOCKET HOUSING	
TREATMENT		APP'D <i>Harumi</i>	SERIES I L - Z		
FINISH					

	(	0	0	I	0	0	I	0	0	C	I	E	2	0	1	1
--	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---

SIZE	A3
------	----

OCF - 116A

DIMENSION		ANGLES	
•	± 0.3	X°	±
• X	± 0.012	X° X°	±
• X	± 0.2		
• X X	± 0.08		
• X X	± 0.1		
• X X X	± 0.04		
		CONCENTRICITY	
		WITHIN T.I.R.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[IL-Z-2S-S125C3](#) [IL-Z-5S-S125C3](#) [IL-Z-10S-S125C3](#) [IL-Z-13S-S125C3](#) [IL-Z-12S-S125C3](#) [IL-Z-15S-S125C3](#) [IL-Z-7S-S125C3](#)