



- Precision engineered and manufactured
- Space saving design for high density packaging
- Micro pins are available in .017 (.43) to .080 (2.03) diameters
- Ideal for mating with our standard line of micro jacks
- Available for press-fit, swage or solder mounting
- Custom micro pins manufactured to your specifications
- Other platings available upon request

SPECIFICATIONS

Material: Brass, ASTM-B16

Plating:

Gold: .000010 per MIL-G-45204, Type II

Tin: .000200 to .000300 per

MIL-T-10727, Type 1


RoHS (RoHS Compliant)

DASH NUMBERS (L Dimension)

- 1 for .032 (.81) thick Board
- 2 for .062 (1.57) thick Board
- 3 for .093 (2.36) thick Board
- 4 for .125 (3.2) thick Board


Example: 1967-1 for .032 (.81) thick Board
1967-2 for .062 (1.57) thick Board

.017 (.43) PIN - SWAGE MOUNT




GOLD	TIN	L	Mtg. Hole
CAT. NO.	CAT. NO.	Length	Dia.
1967-1	1968-1	.051 (1.3)	.052
1967-2	1968-2	.082 (2.0)	(1.32)

.018 (.46) PIN - PRESS-FIT




GOLD	TIN	Mtg. Hole
CAT. NO.	CAT. NO.	Dia.
1986-1	1987-1	.026 (.66)

.018 (.46) PIN - PRESS-FIT



GOLD	TIN	Mtg. Hole
CAT. NO.	CAT. NO.	Dia.
1988-2	1989-2	.026 (.66)


.018 (.46) PIN - PRESS-FIT



GOLD	TIN	Mtg. Hole
CAT. NO.	CAT. NO.	Dia.
1990-2	1991-2	.026 (.66)


MATERIAL:
Phosphor
Bronze

.018 (.46) PIN - PRESS-FIT




GOLD	TIN	A	Mtg. Hole
CAT. NO.	CAT. NO.	Dim.	Dia.
1992-2	1994-2	.243 (6.2)	.022
1993-2	1995-2	.140 (3.6)	(.56)

.020 (.51) PIN - PRESS-FIT




GOLD	TIN	Mtg. Hole
CAT. NO.	CAT. NO.	Dia.
1996-2	1997-2	.040 (1.0)

.020 (.51) PIN - PRESS-FIT




GOLD	TIN	A	Mtg. Hole
CAT. NO.	CAT. NO.	Dim.	Dia.
1998-3	2000-3	.250 (6.4)	.024
1999-3	2001-3	.425 (3.6)	(.61)

.025 (.51) PIN - SWAGE MOUNT




GOLD	TIN	L	Mtg. Hole
CAT. NO.	CAT. NO.	Length	Dia.
1404-1	1424-1	.051 (1.3)	.052
1404-2	1424-2	.082 (2.1)	(1.32)

.025 (.51) PIN - SWAGE MOUNT




GOLD	TIN	L	Mtg. Hole
CAT. NO.	CAT. NO.	Length	Dia.
1408-1	1428-1	.062 (1.6)	.062
1408-2	1428-2	.094 (2.4)	(1.57)

.025 (.51) PIN - SWAGE MOUNT




GOLD	TIN	L	Mtg. Hole
CAT. NO.	CAT. NO.	Length	Dia.
1406-1	1426-1	.047 (1.2)	.035
1406-2	1426-2	.078 (1.9)	(.89)

.025 (.51) PIN - SWAGE MOUNT




GOLD	TIN	L	Mtg. Hole
CAT. NO.	CAT. NO.	Length	Dia.
1407-1	1427-1	.051 (1.3)	.052
1407-2	1427-2	.082 (2.1)	(1.32)

.025 (.51) PIN - SWAGE MOUNT




GOLD	TIN	L	Mtg. Hole
CAT. NO.	CAT. NO.	Length	Dia.
1401-1	1421-1	.065 (1.6)	.043 (1.09)

.040 (1.0) PIN - SWAGE MOUNT




GOLD	TIN	L	Mtg. Hole
CAT. NO.	CAT. NO.	Length	Dia.
1405-1	1425-1	.051 (1.3)	.043
1405-2	1425-2	.082 (2.1)	(1.09)
1405-3	1425-3	.113 (2.9)	

.040 (1.0) PIN - SWAGE MOUNT



GOLD	TIN	L	Mtg. Hole
CAT. NO.	CAT. NO.	Length	Dia.
1402-3	1422-3	.125 (3.2)	.062 (1.57)


.040 (1.0) KAY PIN - PRESS-FIT



MATERIAL:
Solid Nickel Silver
CAT. NO. 1218

Mtg. Hole
.043 (1.09) Dia.


.040 (1.0) HOLLOW PIN - SWAGE MOUNT



MATERIAL:
Brass, Tin Plate
CAT. NO. 1219

Mtg. Hole
.059 (1.50) Dia.


.080 (2.0) PIN - SWAGE MOUNT



Mtg. Hole .094 (2.4) Dia.

GOLD	TIN	A	B	L
CAT. NO.	CAT. NO.	Dim.	Dim.	Dim.
1447-1	1455-1	.335 (8.5)	.156 (4.0)	.051 (1.3)
1447-2	1455-2	.400 (10.2)	.125 (3.2)	.094 (2.4)
1447-3	1455-3	.400 (10.2)	.125 (3.2)	.125 (3.2)
1447-4	1455-4	.400 (10.2)	.125 (3.2)	.156 (4.0)

.040 (1.0) PINS - INSULATED SHORTING PLUG



MATERIAL: Insulator: Plastic, Red or Black
Pins: Brass, Gold Plate

RED	BLACK	A	W
CAT. NO.	CAT. NO.	Dim.	Dim.
1460R	1460B	.200 (5.1)	.375 (9.5)
1461R	1461B	.250 (6.4)	.375 (9.5)
1462R	1462B	.400 (10.2)	.620 (15.7)
1463R	1463B	.500 (12.7)	.620 (15.7)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Keystone Electronics:

[1426-4](#) [1408-4](#) [1427-3](#) [1404-3](#) [1404-4](#) [1406-3](#) [1406-4](#) [1407-3](#) [1407-4](#) [1408-3](#) [1424-3](#) [1424-4](#) [1426-3](#) [1427-4](#)
[1428-3](#) [1428-4](#)