


320 amps Connectors 2-Pole with auxiliary contacts

Catalog Number	Description	Housing Color	Wire AWG	Cable Well Diameter		Cable Size
				in.	mm	sq. mm
E6340G1	Housing with springs 2 contacts & auxiliary contact kit	Gray 36V	2/0	.48	12.3	67.4
E6340G2			3/0	.58	14.7	85.0
E6340G6						35.0
E6341G1		Blue 48V	2/0	.48	12.3	67.4
E6341G2			3/0	.58	14.7	85.0
E6341G6						35.0
E6342G1		Red 24V	2/0	.48	12.3	67.4
E6342G2			3/0	.58	14.7	85.0
E6342G6						35.0
E6343G1		Green 72V	2/0	.48	12.3	67.4
E6343G2			3/0	.58	14.7	85.0
E6343G6						35.0
E6359G1		Black 80V	2/0	.48	12.3	67.4
E6359G2			3/0	.58	14.7	85.0
E6359G6						35.0
E6360G1		Yellow 12V	2/0	.48	12.3	67.4
E6360G2			3/0	.58	14.7	85.0
E6360G6						35.0
E6368G1		Orange 18V	2/0	.48	12.3	67.4
E6368G2			3/0	.58	14.7	85.0
E6368G6						35.0
E6332G1		Brown 96V	2/0	.48	12.3	67.4
E6332G2			3/0	.58	14.7	85.0
E6332G6						35.0
E6333G1		Purple 120V	2/0	.48	12.3	67.4
E6333G2			3/0	.58	14.7	85.0
E6333G6						35.0



C

Housings and Contacts

Catalog Number	Description	Housing Color	Wire AWG	Cable Well Diameter		Cable Size
				in.	mm	sq. mm
E6345G1	Housing with springs & 2 contacts	Gray 36V	2/0	.48	12.3	67.4
E6345G2			3/0	.58	14.7	85.0
E6345G6			# 2	.35	8.9	33.6
E6346G1		Blue 48V	2/0	.48	12.3	67.4
E6346G2			3/0	.58	14.7	85.0
E6346G6			# 2	.35	8.9	33.6
E6347G1		Red 24V	2/0	.48	12.3	67.4
E6347G2			3/0	.58	14.7	85.0
E6347G6			# 2	.35	8.9	33.6

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Anderson Power Products:

[E6332G1](#) [E6333G1](#) [E6340G2](#) [E6341G2](#) [E6342G6](#) [E6343G1](#) [E6343G2](#) [E6343G6](#) [E6345G1](#) [E6345G2](#) [E6345G6](#)
[E6346G6](#) [E6347G1](#) [E6347G2](#) [E6347G6](#) [E6359G1](#) [E6359G2](#) [E6359G6](#) [E6360G1](#) [E6368G1](#)